

International Components Corporation

Tel: 631-952-9595 • 800-645-9154 • Fax: 631-952-9597 • Email: oemsales@icc107.com



GENERAL PURPOSE SQUARE SPEAKER

Part Number: S200SA

MODEL NUMBER	S200SA
FRAME DIAMETER (MM)	50.5 x 50.5
FRAME DEPTH (MM)	18
MATERIAL: CONE / FRAME	PAPER / METAL
MAGNET TYPE	ALNICO
MAGNET: SIZE (MM) / WEIGHT (OUNCES/GRAMS)	13 x 10 - 0.35 / 9.8
RATED POWER (WATTS): Nom. / Max.	0.1 / 0.2
VOICE COIL IMPEDANCE (OHMS)	8 + 15% @ 1000 Hz 1V
RESONANT FREQUENCY (Hz) Without Baffle	450 ± 90
FREQUENCY RESPONSE (Hz)	Fo ~ 5000 ± 10 dB
OUTPUT SOUND PRESSURE LEVEL (S.P.L.)	83.5 ± 2 dB
MEASURED AT:	1W @ 1 M
MEAN VALUE AT:	
OPERATION (MUST BE NORMAL)	0.8K, 1.0K, 1.2K, 1.5K Hz
BUZZ & RATTLES (MUST BE NORMAL)	PROGRAM SOURCE 0.2 W
DISTORTION @ RATED POWER INPUT	SINE WAVE 0.89 V
LOAD TEST (WHITE NOISE)	5% MAXIMUM @ 1,000 Hz
HUMIDITY TEST*	0.1W @ 8 HOURS
	40° ± 2°C 90~95% R.H. 8 HRS

HEAT TEST*	70° ± 2°C 20~50% R.H. 8 HRS
OUTSIDE DIAMETER OF YOKE SEAT (MM)	28 - YOKE SIZE: 22 x 14.2 x 12.5
OUTSIDE DIAMETER (ELIMINATE RIM)	44
BAFFLE OPENING (MM)	44
THICKNESS OF RIM (MM)	2.2
NET WEIGHT (OUNCES)	1.46 / 42.4
MOUNTING DIMENSIONS/DIAGONAL (MM)	56.5 - HOLE SIZE 4 x 4

POLARITY:

DIAPHRAGM SHALL MOVE FORWARD WHEN APPLYING A POSITIVE DC CURRENT TO THE "+" (OR MARKED) TERMINAL.

*SPEAKER MUST MEET NORMAL OPERATION AND BUZZ & RATTLES SPECIFICATIONS

DIMENSIONS

TYPICAL FREQUENCY RESPONSE CURVE

Return to top

All contents are Copyright © 1999 by International Components Corporation, All rights reserved.

This site was developed and is maintained by Promptweb.com. For information, concerns or comments send e-mail to the webmaster. (webmaster@pw2.com)