

## GL-HO-G2 150-865 L60X60

GinoLED HO Module G2 | LED modules for street lighting



### Product family features

- Available with beam angle: 60°×60° and 90°×90°
- Available with color temperature: 4,000 K, 6,500 K
- Color rendering index  $R_a$ : 80
- Impact resistance: IK08
- Type of protection: IP65
- Lifetime (L70/B50): 50,000 h
- Operating temperature range: -30...45 °C
- Certificates: CE, CB, CQC
- Lifetime (L70/B50) for GL-HO 80: 50,000 h (temperature at  $T_p = 50$  °C)
- Lifetime (L70/B50) for GL-HO 120: 50,000 h (temperature at  $T_p = 55$  °C)
- Lifetime (L70/B50) for GL-HO 150/180: 50,000 h (temperature at  $T_p = 60$  °C)

### Product family benefits

- High module efficacy: up to 165 lm/W
- Integrated heat sink for optimal thermal management and tailored optical design
- Light weight design for easy installation

### Areas of application

- Airports, stations and factories
- Indoor courts, exhibition halls, warehouses



# Product datasheet

## Technical data


### Electrical data

Nominal current	0.7 A
Type of current	DC

### Photometrical data

Luminous efficacy	165 lm/W
Color rendering index Ra	>80

### Dimensions & weight



Product weight	2100.00 g
----------------	-----------

### Temperatures & operating conditions

Temperature range in operation at Tc point	-30...45 °C
Temperature range at storage	-40...80 °C

### Certificates & standards

Type of protection	IP65
Standards	Acc. to IEC 62778/Acc. to IEC 60598-1/Acc. to EN 62031/Acc. to EN 55015/Acc. to EN 61547/Acc. to IEC 61000-3-2/Acc. to IEC 61000-3-3

### Logistical data

Commodity code	940540999000
----------------	--------------

### Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	19-10-2022

## Product datasheet

<b>Primary Article Identifier</b>	4062172051576   4062172343978
<b>Candidate List Substance 1</b>	No declarable substances contained
<b>Declaration No. in SCIP database</b>	In work

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172051576	GL-HO-G2 150-865 L60X60	Shipping carton box 1	362 mm x 362 mm x 189 mm	24.77 dm <sup>3</sup>	2896.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.