


# **PB** CONNECTOR





Connector for button batteries used in the compact mobile equipment such as mobile phones. Mounting cost will be reduced by using this connector in place of manual soldering. And, button batteries can be more easily disassembled after use for recycling's sake.

- Resistant to the shock
- Double contact point

## Specifications -

• Applicable batteries: 414 type battery/4.8mm dia. $ imes$ 1.4 height
518 type battery/5.8mm dia. $ imes$ 1.8 height
,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,
614 type battery/6.8mm dia. $ imes$ 1.4 height
621 type battery/6.8mm dia. $ imes$ 2.1 height
<ul> <li>Temperature range: -25°C to +85°C</li> </ul>
(including temperature rise in applying
electrical current)
<ul> <li>Contact resistance: Initial value/100m Ω max.</li> </ul>
After environmental testing/120m $\Omega$ max.
<ul> <li>Insulation resistance: 1,000M Ω min.</li> </ul>
Withstanding voltage: 500V AC/minute
* RoHS compliant products are published.
* Refer to "General Instruction and Notice when using
Terminals and Connectors" at the end of this catalog.


\* Contact JST for details.

## Standards


Recognized E60389

#### PC board layout (viewed from component side)


#### PB-414SR12K-TF




#### PB-414SS12-TF




PB-614SS13-TF PB-621SR13-TF



#### PB-518SR13-TF



# **PB CONNECTOR**




Holder part	Model No.	Q'ty/ reel
Resin hook	PB-414SR12K-TF	3,000
Resin hook	PB-414SS12-TF	3,000
Resin hook	PB-518SR13-TF	2,000
Resin hook	PB-518SW13-TF	2,000
Resin hook	PB-614SS13-TF	2,000
Resin hook	PB-621SR13-TF	2,000
	Resin hook Resin hook Resin hook Resin hook	Resin hook         PB-414SS12-TF           Resin hook         PB-518SR13-TF           Resin hook         PB-518SW13-TF           Resin hook         PB-614SS13-TF

Material and Finish

Contact: Copper alloy, nickel-undercoated, gold-plated Housing: Glass-filled LCP, UL94V-0, natural (ivory), black (414 type) Holder contact: Copper alloy, nickel-undercoated, gold-plated (614 type with metal hook)

# **PB** CONNECTOR

### Taping specifications



Model No.	Taping dimensions (mm)		Reel dimensions (mm)		Q'ty/
	F	W	W1	W2	reel
PB-414SR12K-TF	7.5	16.0	16.4	330	3,000
PB-414SS12-TF	7.5	16.0	16.4	330	3,000
PB-518SR13-TF	7.5	16.0	16.4	380	2,000
PB-518SW13-TF	7.5	16.0	16.4	380	2,000
PB-614S13-TF	11.5	24.0	24.4	380	2,000
PB-614SS13-TF	11.5	24.0	24.4	330	2,000
PB-621SR13-TF	11.5	24.0	24.4	380	2,000

#### Note:

- 1. Specifications conform to JIS C 0806. The tape width, connector loading recess square hole dimensions, etc. are determined by the number of circuits and external shape of the connector to be loaded.
- 2. Specifications are subject to change without prior notice.