


D

C

B

A

4




LED (XT-E)

Detail B


Scale: 5:1

3



Section view A-A



Scale: 1:1



Isometric view

Scale: 1:1

2



4

3

2


INDEX	PART NO	DESCRIPTION	MATERIAL	COLOUR
1	ANNA-40-7-WW		PMMA	

Tolerances if not otherwise shown  
According to DIN ISO 2768-1  
Linear measures:  
Up to 30mm class F, otherwise class M.  
According to DIN ISO 2768-2  
Form and position: class K

LEDiL

Ledil Oy  
Salorankatu 10  
FIN 24240 SALO  
Finland

THIRD ANGLE PROJECTION:



DRAWING TITLE

ANNA-40-7-WW

This drawing is the property  
of LEDiL Oy. It may not be  
reproduced, copied or  
communicated without a written  
agreement with LEDiL Oy."

SIZE PART NUMBER

A4

-

SCALE	1:1	WEIGHT	9,34 g	SHEET	1/1
-------	-----	--------	--------	-------	-----

D

A

1