


Ordering number C12786_STRADA-K

Family	Strada-K	FWHM	Asym degrees
Type	Lens	Efficiency	96 %
LED	XT-E	cd/lm	1.100
Color	Clear	Gerber File	Available
Diameter	19.6 + 15.5 mm		
Height	8.7 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	Screw, pin, glue		
Status	Ready		

Ordering number CA12787_STRADA-K

Family	Strada-K	FWHM	Asym degrees
Type	Assembly	Efficiency	96 %
LED	XT-E	cd/lm	1.160
Color	Clear	Gerber File	Available
Diameter	19.6 + 15.5 mm		
Height	8.8 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Strada-K series

last update 22/10/2012

GENERAL INFORMATION


- Product series especially designed & optimized for XT-E series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:


http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

Absolute intensity of C12786_STRADA-K_(XT-E)



Absolute intensity of CA12787_STRADA-K_(XT-E_AWT)



D


C

B


A

4

4




Isometric view




Bottom view

3

3




PCB-suggestion



Front view

2

2



Top view

Material: PMMA

Tolerances for dimensions:
 0-20mm tolerance value $\pm 0.1\text{mm}$
 21-45mm tolerance value $\pm 0.2\text{mm}$
 46-90mm tolerance value $\pm 0.3\text{mm}$
 91-100mm tolerance value $\pm 0.4\text{mm}$
 101-mm tolerance value $\pm 0.5\text{mm}$

This drawing is our property.
 It can't be reproduced
 or communicated without
 our written agreement.



Ledil Oy
 Salorankatu 10
 FIN 24240 SALO
 Finland

DRAWING TITLE

Datasheet STRADA-K

DRAWN BY
 mav

DATE
 18.04.2012

CHECKED BY
 sn

DATE
 18.04.2012

SIZE A4 DRAWING NUMBER C12786

REV
 1

DESIGNED BY
 mav

DATE
 06.03.2012

SCALE 1:1 WEIGHT (g)

SHEET 1/1


D

A

1

1


Luminaire: LEDiL OY C12786_STRADA-K_(XT-E) Eff. 96%
Lamps: 1 x Cree XT-E AWT (100lm@250ma)



cd/klm

— C0 - C180 — C90 - C270

Luminaire: LEDiL Oy CA12787_STRADA-K_(XT-E_AWT) Eff. 96%
Lamps: 1 x Cree XT-E AWT (99,67lm@250mA)



cd/klm

— C0 - C180 — C90 - C270