







PC Board Layout - Component Side

● = Pin 1

Specifications

Description AJT14G

USB B
Vertical mount
4 positions

Technical Data AJT14G

Housing: PBT
Contact: Phosphor bronze ($t=0.25\text{mm}$)
Gold/tin plated
Ni:1~1.5u; Tin:3u, Gold:30u
Metal Shell: Brass ($t=0.3\text{mm}$)
Nickel plated
Ni:2~3u

Ordering Information

AJT14G	4	4	1	3 - 0	0	X
Type	Positions	Contacts	Ports	Plating	Insert	
				1=6u"	1=Black	
				3=30u"	2=White	

Tolerance

unless otherwise specified

.0 $\pm$.30
.00 $\pm$.20
.000 $\pm$.075

RIA CONNECT	P/N: AJT14G4413-00X
Desc.: USB Type B, Vertical Thru Hole	
Date: 7-17-06	Drawn By: Donna Mears
Dimensions in mm	Verified By: Mike Balekdjian