

<p>0291</p> <p>0291-0-15-XX-16-XX-10-0 Hex press-fit in 1,7 plated thru hole</p>	<p>0293</p> <p>0293-0-15-XX-16-XX-10-0 Press-fit in 1,7 mounting hole</p>	<p>0287</p> <p>0287-0-15-XX-16-XX-10-0 Solder mount in 1,65 min. mounting hole Also available on 8mm wide carrier tape: 3,250 parts per 330mm reel. Order as: 0287-0-57-XX-16-XX-10-0</p>	<p>0285</p> <p>0285-0-15-XX-16-XX-10-0 Solder mount in 1,65 min. mounting hole</p>
--	---	---	--

<p>0284</p> <p>0284-0-15-XX-16-XX-10-0 Solder mount in 1,78 min. mounting hole</p>	<p>8114</p> <p>8114-0-15-XX-16-XX-04-0 Press-fit from underside of pc board into 1,65 mounting hole</p>	<p>0407</p> <p>0407-0-15-XX-16-XX-04-0 Press-fit in 1,68 mounting hole</p>	<p>0415</p> <p>0415-0-15-XX-16-XX-10-0 Solder mount in 1,6 min. mounting hole Also available on 24mm wide carrier tape: 1,500 parts per 330mm reel. Order as: 0415-0-57-XX-16-XX-10-0</p>
--	---	--	---

<p>0303</p> <p>0303-0-19-XX-16-XX-10-0 Wire Termination Press-fit in 1,70 mounting hole</p>	<p>0306</p> <p>0306-0-19-XX-16-XX-10-0 Wire Termination #18 gage crimp barrel</p>	<p>0273</p> <p>0273-0-15-XX-16-XX-10-0 Press-fit in 1,98 mounting hole</p>	<p>7520</p> <p>7520-0-15-XX-16-XX-10-0 Press-fit in 1,68 mounting hole</p>
---	---	--	--

<p>SPECIFICATIONS</p> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±0,13 DIAMETERS: ±0,05 ANGLES: ± 2°</p>	<p>ORDER CODE: XXXX - X - 1X - XX - 16 - XX - XX - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH:</p> <p>01 5,08µm TIN/LEAD OVER NICKEL</p> <p>80 5,08µm TIN OVER NICKEL ◇</p> <p>15 0,25µm GOLD OVER NICKEL ◇</p> <p>CONTACT →</p> <p>#16 CONTACT (DATA ON PAGE 221)</p>	<p>SPECIFY CONTACT FINISH:</p> <p>01 5,08µm TIN/LEAD OVER NICKEL</p> <p>80 5,08µm TIN OVER NICKEL ◇</p> <p>27 0,76µm GOLD OVER NICKEL ◇</p>
--	---	---

