

Resonators > CERALOCK (MHz) > Part Number

How to check EU RoHS Compliant of Our Products is [here](#).

<a href="#">Product Lifecycle Stage</a>	in Production
<a href="#">Recommended Rank</a>	Preferred














### Specification

Global Part Number	CSTCE16M0V53C-R0
Previous Part Number	
Nominal Frequency	16.000MHz
Initial Tolerance	±0.5%
Temp. Stability	±0.15%
Temperature Range	-40 to +125°C
Wash	Available
Ultrasonic Wash	Available
Built-in Load Capacitance	15pF
Use	For automotive electronics

### Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	3000
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

### Details

- ?  [Part Numbering](#)
- ?  [Appearance](#)
- ?  [Dimensions](#)
- ?  [Features, Applications](#)
- ?  [Temperature Characteristics](#)
- ?  [Basic Oscillation Circuit](#)
- ?  [Standard Land Pattern Dimensions](#)
- ?  [Notice \(storage and operating condition\)](#)
- ?  [Notice \(rating\)](#)
- ?  [Notice\(Soldering and Mounting\)](#)
- ?  [Notice \(handling\)](#)
- ?  [Packaging](#)
- ?  [Minimum\\_Quantity\[Supplementation\]](#)

Please approve our product specifications or to transact the approval sheet for product specifications before ordering. Please read rating and !Cautions first. Product specifications in this catalog are as of January 2008.

All products and company names herein are trademarks or registered trademarks of their respective owners.