



Region
 > Global > North America > Europe

English | 中文

Part Number Search

Home	Products	Search	Support	Ab
------	----------	--------	---------	----

[Home](#) > [Search Engine](#) > Catalog: CSTCR4M00G55-R0

Resonators > CERALOCK (MHz) > Part Number

How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specifications

Global Part Number	CSTCR4M00G55-R0
Previous Part Number	
Nominal Frequency	4.000MHz
Initial Tolerance	±0.5%
Resonant Frequency	60ohm
Temp. Stability	±0.2%
Operating Temperature Range	-20 to +80°C
Frequency Aging	±0.1%
Wash	Not Available
Ultrasonic Wash	Not Available
Built-in Load Capacitance	39pF
Use	For consumer electronics

Details

- [Part Numbering](#)
- [Appearance](#)
- [Dimensions](#)
- [Features and Applications](#)
- [Temperature Characteristics](#)
- [Basic Oscillation Circuit](#)
- [Standard Land Pattern](#)
- [Notice_ \(Storage and Operating Conditio](#)
- [Notice_\(Rating\)](#)
- [Notice_\(Soldering and Moun](#)
- [Notice_\(Handling\)](#)
- [Packaging](#)
- [Minimum Quantity](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	3000
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	



Please approve our product specifications or to transact the approval sheet for product specifications before ordering.

Please read rating and !Cautions first.

Product specifications in this catalog are as of November 2009

Please make sure to read the Murata's [Product Policy](#) ,too.

All products and company names herein are trademarks or registered trademarks of their respective ow

| [Site Map](#) | [History](#) | [Terms of use](#) | [Privacy Policy](#) |

All Rights Reserved, Copyright© Murata Manufac