



Product Number: LFD21859MDP2A076

Specifications

Application	CDMA
Frequency Range{P1}(f1)	859MHz $\pm$ 35.0MHz
Frequency Range{P2}(f2)	1920MHz $\pm$ 70.0MHz
Insertion Loss(I (P1-P3 in f1)	0.40dB max. (at 25°C)
Insertion Loss(II (P1-P3 in f1)	0.50dB max. (-40~+85°C)
Insertion Loss(I (P2-P3 in f1)	0.45dB max. (at 25°C)
Insertion Loss(II (P2-P3 in f1)	0.55dB max. (-40~+85°C)
Attenuation{P1-P3}(in f2)	20dB min.
Attenuation{P2-P3}(in f1)	19dB min.
VSWR {P1} (in f1)	1.7 max.
VSWR{P2} (in f2)	1.7 max.
VSWR {P3} (in f1,f2)	1.7 max.
Power Capacity	3W max.
Min. of Operating Temperature Range	-40°C
Max. of Operating Temperature Range	+85°C

Minimum Quantity

180mm Embossed Tape	4000
---------------------	------