



Region
 > Global > North America > Europe

English | 中文(简体) | 日本語

Part Number Search

Search

Home

Products

Search

Support

About Us

[Home](#) > [Search Engine](#) > Catalog: PVG5A203C03R00

Resistors > Trimmer Potentiometers > SMD Sealed Type Multi-turns
















How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specifications

Global Part Number	PVG5A203C03R00
Previous Part Number	
Power Rating	0.25W(70°C)
Maximum Working Voltage	300Vdc
Resistance Taper	B (Linear)
Contact Resistance Variation	Less than 3% of total resistance value or 3ohm, whichever is greater
Residual Resistance	Less than 1% of total resistance value or 2ohm, whichever is greater
Adjustment Direction	Top
Soldering Method	Reflow/Soldering Iron
Size	5mm
Auto Adjustment	No
Number of Turns (Effective Rotation Angle)	11
Torque	17.6mN·m max.
Total Resistance Value	20k ohm ±10%
TCR	±150ppm/°C
Operating Temperature	-55 to +125°C
Mass	0.18g

Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Features and Applications](#)
-  [Specifications](#)
-  [Construction](#)
-  [Land Pattern](#)
-  [Taping Dimensions](#)
-  [Reel Dimensions](#)
-  [Notice \(Storage and Operating Condition\)](#)
-  [Notice\(Rating\)](#)
-  [Notice \(Soldering and Mounting\)](#)
-  [Notice \(Handling\)](#)
-  [Notice\(Other\)](#)
-  [Soldering Profile](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	250
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Please approve our product specifications or to transact the approval sheet for product specifications before ordering.

Please read rating and !Cautions first.

Product specifications in this catalog are as of March 2010

Please make sure to read the Murata's [Product Policy](#) ,too.

All products and company names herein are trademarks or registered trademarks of their respective owners.

UP 

[| Site Map](#) | [| History](#) | [| Terms of use](#) | [| Privacy Policy](#) |

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.