

Sp OBSOLETE- See P/N PSR-57N08A01-AQ

Voice Coil Impedance (Ω)	$8 \pm 15\%$ at 800 Hz / 1.0 V
Rated Input (W)	0.25
Max. Input (W)	1.0
Lowest Resonance Freq Fo (Hz)	$600 \pm 20\%$
Frequency Range (Hz)	Fo ~ 4000
Output S.P.L. (dB)	92 ± 3 at 1W 1M .8k, 1k, 1.2k, 1.5kHz
Magnet Size (mm)	$\varnothing 12.5 * 1.5$
Magnet	Ferrite
Core Material Mylar	Paper
Frame Material	Metal
Operation / Storage Temp	-25 to 50°C
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant

