

PIN RECEPTACLES

PIN RECEPTACLES WITH ORGANIC FIBRE PLUG® SOLDER BARRIER (SEE SPECIFIC CONTACT RANGE ON PAGES 254 - 262)

<p>0337 0337-0-XX-XX-15-XX-10-0 Solder mount in $\varnothing .066" \pm .003"$ PTH #15 Contact for $\varnothing .020" - .032"$ pins Also available on 8mm wide carrier tape: 6,000 parts per 13" reel</p>	<p>4280 4280-0-XX-XX-16-XX-10-0 Solder mount in $\varnothing .067" \pm .003"$ PTH #16 Contact for $\varnothing .022" - .034"$ pins Also available on 8mm wide carrier tape: 6,000 parts per 13" reel</p>	<p>5280 5280-0-XX-XX-16-XX-40-0 Solder mount in $\varnothing .067" \pm .003"$ PTH #16 Contact for $\varnothing .022" - .034"$ pins Also available on 16mm wide carrier tape: 2,200 parts per 13" reel</p>	<p>0332 0332-0-XX-XX-18-XX-10-0 Solder mount in $\varnothing .079" \pm .003"$ PTH #18 Contact for $\varnothing .037" - .043"$ pins Also available on 16mm wide carrier tape: 2,200 parts per 13" reel</p>
<p>0479 0479-0-XX-XX-34-XX-10-0 Solder mount in $\varnothing .077" \pm .003"$ PTH #34 Contact for $\varnothing .032" - .046"$ pins Also available on 16mm wide carrier tape: 2,200 parts per 13" reel</p>	<p>0375 0375-0-XX-XX-02-XX-10-0 Solder mount in $\varnothing .087" \pm .003"$ PTH #02 Contact for $\varnothing .040" - .050"$ pins Also available on 12mm wide carrier tape: 4,500 parts per 13" reel</p>	<p>0353 0353-0-XX-XX-03-XX-10-0 Solder mount in $\varnothing .106" \pm .003"$ PTH #03 Contact for $\varnothing .040" - .060"$ pins Also available on 12mm wide carrier tape: 1,300 parts per 13" reel</p>	<p>0384 0384-0-XX-XX-23-XX-10-0 Solder mount in $\varnothing .105" \pm .003"$ PTH #23 Contact for $\varnothing .045" - .065"$ pins Also available on 12mm wide carrier tape: 2,000 parts per 13" reel</p>
<p>0376 0376-0-XX-XX-07-XX-10-0 Solder mount in $\varnothing .133" \pm .003"$ PTH #07 Contact for $\varnothing .065" - .082"$ pins Also available on 16mm wide carrier tape: 1,500 parts per 13" reel</p>	<p>0321 0321-0-XX-XX-08-XX-10-0 Solder mount in $\varnothing .144" \pm .003"$ PTH #08 Contact for $\varnothing .084" - .102"$ pins Also available on 16mm wide carrier tape: 1,700 parts per 13" reel</p>	<p>3435 3435-0-XX-XX-47-XX-04-0 Solder mount in $\varnothing .046" \pm .003"$ PTH #47 Contact for $\varnothing .025" - .036"$ and .025" square pins</p>	

SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard
Contact Material: Beryllium Copper Alloy 172, HT
Solder Barrier: Organic Fibre Plug®
Dimensions: Inches
Tolerances On: Lengths: $\pm .005$
 Diameters: $\pm .002$
 Angles: $\pm 2^\circ$



ORDER CODE: XXXX - 0 - XX - XX - XX - XX - 0

BASIC PART

SPECIFY PACKAGING:

- 43 Discrete Receptacles
- 67 Supplied on 13" Reels

SPECIFY SHELL FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- 80 200 μ " TIN OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 27 30 μ " GOLD OVER NICKEL (RoHS)
- 02 100 μ " TIN/LEAD OVER NICKEL
- 84 200 μ " TIN OVER NICKEL (RoHS)

CONTACT:

#02, #07, #08, #15, #16, #18, #23, #34 or #47 CONTACT (DATA ON PAGES 254 - 262)

