


THIRD ANGLE PROJECTION




NN - # Of Conductors
LLLL - Cable Length

Conductors	Tin Plated Copper
Insulation	Polyester
Voltage	90 V
Temperature	-55° C to 105° C
UL Flame Rating	VW-1
Dielectric Strength	5,000 V
Insulation Resistance	5,000 Mega Ohms

Part Number	050P3NNKLLLL-406406	100P3NNDLLLL-510510	125P3NNCLLLLL-510510	127P3NNCLLLLL-510510	254P3NNALLL-510510	Tolerance On Cables With Pitch	
						>0.50mm	0.50mm
Pitch	0.5 mm	1.00 mm	1.25 mm	1.27 mm	2.54 mm	±0.15mm	±0.10mm
Cable Width	(N+1) 0.50	(N+1)	(N+1) 1.25	(N+1) 1.27	(N+1) 2.54	±0.15mm	±0.10mm
Cable Thickness	0.22	0.25	0.25	0.25	0.25	±0.05mm	
Conductor Width	0.28	0.66	0.80	0.80	1.57	±0.05mm	
Conductor Thickness	0.035	0.076	0.076	0.076	0.076	±0.025mm	
Exposed Length	4	5	5	5	5	±1.00mm	
Stiffener Length	6	10	10	10	10	±1.50mm	
Mating Thickness	0.30	0.30	0.30	0.30	0.30	±0.05mm	
Margin	0.36	0.66	0.85	0.86	1.68	±0.15mm	±0.10mm

Tolerance On Length	
0-150 mm	±1.50 mm
151-300 mm	±1.75 mm
301-450 mm	±2.50 mm
451-600 mm	±3.00 mm
601-900 mm	±4.00 mm
Over 900 mm	±1% Of Length

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND THE DESIGN AND IDEAS EMBODIED TO THE DEVICE TO WHICH IT RELATES AND THE METHODS OF PRODUCING THE DEVICE ARE THE PROPERTY OF NICOMATIC LP., AND SHALL NOT BE EMPLOYED, COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY IN ANY MANNER, EITHER WHOLLY OR IN PART, WITHOUT THE PRIOR WRITTEN CONSENT OF NICOMATIC LP.

UNLESS OTHERWISE SPECIFIED		APPROVALS	DATE	 (215) 444-9580 One Ivybrook Blvd. Unit 120, Warminster PA 18974 Fax (215) 444-9581
METRIC DIMENSIONS		DRAWN G. HICKS	03/21/05	
TOLERANCES STATED ABOVE		APPROVED D. FISHER	03/21/05	STANDARD CARD CABLE STYLE P3
MATERIAL SEE NOTES				
FINISH SEE NOTES				SIZE A DWG NO. C100710 REV --
DO NOT SCALE DRAWING				SCALE: NONE FILE NO. C100710 SHEET 1 OF 1