


THIRD ANGLE PROJECTION




OF CONDUCTORS= 20
 PITCH= 1.27 ±0.15
 CABLE WIDTH= 26.67±0.15
 CABLE THICKNESS= 0.25 ±0.05
 INSULATION= POLYESTER

Tolerance On Length	
0-500 mm	±1.50 mm
501-900 mm	±3.00 mm
Over 900 mm	±0.5% Of Length

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND THE DESIGN AND IDEAS EMBODIED TO THE DEVICE TO WHICH IT RELATES AND THE METHODS OF PRODUCING THE DEVICE ARE THE PROPERTY OF NICOMATIC LP, AND SHALL NOT BE EMPLOYED, COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY IN ANY MANNER, EITHER WHOLLY OR IN PART, WITHOUT THE PRIOR WRITTEN CONSENT OF NICOMATIC LP.

UNLESS OTHERWISE SPECIFIED	APPROVALS	DATE
METRIC DIMENSIONS	DRAWN C. Somozg	05/14/09
TOLERANCES STATED ABOVE	APPROVED D.Fisher	05/14/09
MATERIAL	SEE NOTES	
FINISH	SEE NOTES	
DO NOT SCALE DRAWING		



Tel. (215) 444-9580
 Fax (215) 444-9581

1 Ivybrook Blvd Unit 120, Warminster PA 18974

JUMPER CABLE, SOLDER TABS

SIZE A	DWG NO. SS090506-0130A	REV ---
SCALE : NONE	FILE NO. 100791	SHEET 1 OF 1