



DESCRIPTION: 6 PIN MINI-DIN SHIELDED JACK - PURPLE




MATERIALS:
 HOUSING: PA46 - UL 94V-0
 COLOR: PC99 PURPLE
 SHIELD: BRASS - NICKEL PLATED
 CONTACT: PHOSPHOR BRONZE
 CONTACT: UNDER PLATE 50u' MIN
 NICKEL OVER ALL, 120u' MIN TIN/
 ON SOLDER TAILS, GOLD FLASH
 IN MATING AREA



ELECTRICALS:
 CONTACT CURRENT RATING: 1 AMP
 INSULATION RESISTANCE: 500 MEGA-
 OHMS MIN.
 DIELECTRIC WITHSTANDING VOLTAGE:
 500V AC RMS FOR 1 MINUTE
 OPERATING TEMPERATURE:
 -25°C TO +70°C

BOTTOM VIEW

STANDARD TOLERANCES	
.X	= ± .015
.XX	= ± .010
.XXX	= ± .005
ANGLES	= ± 0° 30'

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: PAM JENKINS	DATE: 10-07-06	
	<h1>NorComp</h1>			CHECKED:	DATE:
SCALE:				SHEET 1 OF 1	REV 1
DWG NO. 251-006-213LP01					