


#4-40 X 7/16" FILLISTER HEAD MACHINE SCREW  
MATERIAL - STEEL  
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
QTY: 2 EACH



#4-40 #2 BLANK HEX NUT  
MATERIAL - STEEL  
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
QTY: 2 EACH



#4-40 X 1/2" FILLISTER HEAD CAPTIVE SCREW  
MATERIAL - STEEL  
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
QTY: 2 EACH




#4 SADDLE WASHER  
MATERIAL - STEEL  
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)  
QTY: 2 EACH

THIS IS A CONTROLLED DOCUMENT AND IS SUBJECT TO CHANGE. CONTACT NORTHERN TECHNOLOGIES ENGINEERING FOR THE LATEST REVISION.

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	A	ECN 0553	20-MAY-05	
	B	ECN 0601	10-AUG-06	

NO LOGO



NORTECH LOGO



PART NUMBER INFORMATION

PART#	LOGO STYLE	SUPPLIED
A30E320000	NO LOGO	BULK
C88E320000	NO LOGO	PACKAGED
A30E321000	NORTECH LOGO	BULK
C88E321000	NORTECH LOGO	PACKAGED

CONNECTOR COVER:

1. MATERIAL: ABS COMPOUND - UL94HB
2. FINISH: NICKEL PLATING PER NTC SPECIFICATION N/T 000500
3. DIMENSIONS: INCHES [MM]
4. TOLERANCE: ±0.015 [0.381]

COMPRESSION INSERT TREE

1. MATERIAL: THERMOPLASTIC
2. COLOR: BLACK
3. DUROMETER: 75 ±5 TYPE A PER ASTM D2240
4. DIMENSIONS: INCHES [MM]
5. TOLERANCE: ±0.020 [0.508]

UNLESS OTHERWISE SPECIFIED  
1. ALL DIMENSIONS ARE IN INCHES (MM)  
2. DIMENSIONS ARE TYPICAL

**Northern Technologies**

THIS DRAWING IS THE PROPERTY OF NORTHERN TECHNOLOGIES AND SHOULD NOT BE REPRODUCED WITHOUT NORTHERN TECHNOLOGIES WRITTEN PERMISSION.

DRAWN JSD		10-FEB-05		PART NUMBER SEE PART NUMBER INFORMATION	
CHECKED SCN		10-FEB-05		DESCRIPTION CMP 25 STR EXIT TWO PIECE METALIZED PLASTIC COVER	
ISSUED		10-FEB-05		SIZE B	CODE 200_133
		SCALE 1:1		DWG NO. 0002-200-133	REV
				SHEET 1 OF 1	