



NXP 72 MHz, 32-bit Cortex-M3™ microcontrollers LPC1300

Low-power Cortex-M3 based microcontrollers simplify USB designs

The LPC1300 series includes USB based LPC134x and low power LPC1300L microcontrollers. The LPC1340 includes on-chip USB drivers for mass storage class (MSC) and human interface device (HID). This greatly simplifies USB implementations since the USB drivers are incorporated in ROM, and saves around 5-6 Kbytes of user code. The LPC1300L includes power profiles in ROM and offers low active power consumption at approximately 170 uA/MHz.

Key features

- ▶ ARM Cortex-M3 processor
 - 72 MHz operation
 - Nested Vectored Interrupt Controller for fast deterministic interrupts
 - Wakeup Interrupt Controller allows automatic wake from an priority interrupt
 - Three reduced-power modes: Sleep, Deep-sleep, and Deep power-down
- ▶ Memories
 - Up to 32 KB Flash memory
 - Up to 8 KB SRAM
- ▶ Serial peripherals
 - USB 2.0 full-speed device controller with on-chip PHY
 - UART with fractional baud rate generation, internal FIFO, and RS-485 support
 - 1-2 SSP/SPI controller with FIFO and multi-protocol capabilities
 - I²C-bus interface supporting full I²C-bus specification and Fast-mode plus with a data rate of 1 Mbit/s, multiple address recognition, and monitor mode
- ▶ Analog peripherals:
 - 10-bit analog-to-digital converter (ADC) with eight channels and conversion rates up to 400 K samples per second
- ▶ Other peripherals:
 - Up to 42 General Purpose I/O (GPIO) pins with configurable pull-up/down resistors and a new, configurable open-drain operating mode
 - Four general-purpose counter/timers, with a total of four capture inputs and 13 match outputs
 - Programmable Watchdog timer (WDT) with lock-out feature
 - System tick timer
 - Each peripheral has its own clock divider for power savings

Applications

- ▶ White goods
- ▶ e-Metering
- ▶ Consumer peripherals
- ▶ Remote sensors
- ▶ 16/32-bit applications



Built around a Cortex-M3 Rev2 processor core, the LPC1300 is equipped with up to 32 KB of Flash and up to 8 KB of SRAM, uses a single 3.3 V power supply (for operation between 2.0 and 3.6 V), and is available in LQFP48 or HVQFN33 packages.


The LPC1300 series is pin-to-pin compatible with the LPC1100 series, NXP's new family of Cortex-M0 MCUs, so it gives designers a straightforward migration path to the even lower-power features of the Cortex-M0 architecture.

Also, in keeping with NXP's existing line of more than 50 USB-equipped ARM MCUs, the LPC134x offers support for USB full-speed operation. HID and mass storage USB driver software is included in a dedicated on-chip ROM, maximizing the amount of Flash memory available for user code.

Tools

The LPC1300 series is supported by LPCXpresso, an easy-to-use, comprehensive development tool platform for under US\$30. It's also supported by development tools from IAR, Keil, Hitex, Code Red, and many others. For the most current listing, please visit www.nxp.com/microcontrollers.


LPCXpresso supports all Cortex-M devices



LPC1300L (LPC131x/01) include the following enhancements:

- ▶ Power profiles enable lower power consumption in Active and Sleep modes
- ▶ Four levels for BOD forced reset
- ▶ Second SSP controller
- ▶ Windowed Watchdog Timer (WWDT)
- ▶ Internal pull-up resistors pull up pins to full V_{DD} level
- ▶ Programmable pseudo open-drain mode for GPIO pins

LPC1300 block diagram



* LPC134x only

LPC1300 selection guide

Type number	Flash	Total SRAM	USB	UART RS-485	I2C/Fast+	SSP/SPI	ADC channels	Packages
LPC1343	32 KB	8 KB	Device	1	1	1	8	LQFP48, HVQFN33
LPC1342	16 KB	4 KB	Device	1	1	1	8	HVQFN33
LPC1313/01	32 KB	8 KB	-	1	1	2	8	LQFP48, HVQFN33
LPC1311/01	8 KB	2 KB	-	1	1	2	8	HVQFN33

www.nxp.com

© 2011 NXP Semiconductors N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Date of release: June 2011

Document order number: 9397 750 17136

Printed in the Netherlands