



Part Number: OPB811L55

WIDE GAP SLOTTED OPTICAL SWITCH

Package	Slotted L
Slot Width / Depth:	0.375" / 0.350"
Aperture Emitter / Sensor:	0.05" / 0.05"
Wavelength (nm) (Type):	890
I_F (mA) Typ / Max:	20 / 50
Light Current I_{C(ON)} (mA) Min / Max:	1.0 / NA
V_{CE} (V) (Max):	30
Lead Length / Spacing:	0.425" / 0.570"
RoHS:	Yes