



Part Number: OPB811W55Z

Wire Termination Wide Gap Slotted Optical Switch

Package	Slotted T
Wavelength (nm) (Type):	890
Slot Width / Depth:	0.375" / 0.350"
Aperture Emitter / Sensor:	0.05" / 0.05"
I_F (mA) Typ / Max:	17 / 75
Light Current I_{C(ON)} (mA) Min/Max:	1.0 / NA
V_{CE} (V) (Max):	30
Lead Length / Spacing:	24" / 26 AWG Wire
RoHS:	Yes