



Product Number: **DNF18-205FIB-M**

▪ RoHS Compliancy Status	Compliant
▪ Part Description	Female disconnect, nylon fully insulated, funnel entry, 22 – 18 AWG, .205 X .032 tab size.
▪ Product Type	Disconnects
▪ CSA Certified	Yes
▪ UL Listed	Yes
▪ Height (In.)	.22
▪ Height (mm)	5.6
▪ Length (In.)	.78
▪ Length (mm)	19.8
▪ Width (In.)	.31
▪ Width (mm)	7.9
▪ Max. Ins.	.136
▪ Max. Ins. (mm)	3.5
▪ Panduit Color Code	Red

▪ Pricing Description	Female Disconnect, nylon fully insulated, 22 - 18 AWG, .187/.205 x .032 tab size, funnel entry
▪ Tab Size (In.)	.205/.187 x .032
▪ Tab Size (mm)	5.2/4.7 x .8
▪ Tool	CT-100A, CT-600-A, CT-1525‡, CT-2500‡
▪ Wire Range	22 – 18 AWG
▪ Wire Range (mm²)	0.5 – 1.5
