

Xitanium Constant Voltage Outdoor

LED Power Driver Outd. 100-240V 100W 24V

Constant Voltage Outdoor LED drivers deliver a highly stable output voltage and are SELV (Safety Extra Low Voltage) compliant. These drivers are the perfect choice for enabling easy modular connection of multiple LED PCBs in parallel. The Constant Voltage Outdoor category offers excellent reliability and ensures a simplified installation process. Robust design reduces maintenance and lowers the cost of ownership over the application lifetime.

Product data

• General Characteristics

Input Frequency 50/60 Hz IP Classification IP66 Lifetime 90% 50000 hr

surv.@Tcaselife

Housing Color White

• Operating Characteristics

Efficiency Range Power Factor (100% 0.9 (min) -

120 W Input Power max Output Voltage 24.3 V

Range

Output Current 4100

Range (mA)

Total Harmonic 20 (max) % Distortion IEC

1340 (max) mA Input Current max Inrush Current Peak 105 (max) A Inrush Current 196 us

Width to 50% Type of Dimming

None 100-240 V Input Voltage Range (AC)

Output Voltage -5 (min), 5 (max) %

Tolerance

Wiring Characteristics

Wire Connection on driver to L2

300 mm Input Wire Length Input Wire Diameter 0.82 mm2 Output Wire Length 300 mm

Output Wire Diam-

0.82 mm2

eter

• Temperature Characteristics

T-case Lifetime 85 (max) C T-case maximum

-30 (min), 60 (max) C T-ambient T-Storage -40 (min), 85 (max) C

• Product Dimensions

Length A1 241 mm Width B1 43 mm Height C1 30 mm Fixing Hole Diameter 4.4 mm

D1

Fixing Hole Distance 26.6 mm

Width B2

Fixing Hole Distance 228.6 mm

Length A2

· Approval&Application Chars

Isolation classification Class II ENEC certificate Νo CE marking Yes

Product Data

Order code 913700621091 913700621091 Full product code

Full product name LED Power Driver Outd. 100-240V

100W 24V

Order product name LED Power Driver Outd. 100-240V

100W 24V

Pieces per pack





Xitanium Constant Voltage Outdoor

Packing configuration Packs per outerbox 10


10 8711500911964 Bar code on pack -EAN1 Bar code on 8711500911971


outerbox - EAN3

Logistic code(s) - 12NC 913700621091

Net weight per piece 0.638 kg


Dimensional drawing





LED Power Driver Outd. 60 & 100 W

Product	A1 (Norm)	A2 (Norm)	B1 (Norm)	B2 (Norm)	C1 (Norm)	D1 (Norm)
LED Power Driver Outd. 100-240V 100W 24V	241	228.6	43	26.6	30	4.4



LED Power Driver Outd. 60 & 100W



© 2012 Koninklijke Philips Electronics N.V. All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.