



Find your ideal combination

Philips Fortimo and Lexel modules, drivers and cables

December 2011

PHILIPS
sense and simplicity

Content

Fortimo LED decorative modules

Fortimo LED disk modules

Fortimo LED downlight module (DLM)

Fortimo LED downlight module (DLM) Food

Fortimo LED downlight module Twistable (TDLM)

Fortimo LED integrated spot module

Fortimo LED high brightness module (HBM)

Fortimo LED linear light module (LLM)

Fortimo LED linear light module Solar (LLM)

Fortimo LED spotlight module (SLM) Gen1

Fortimo LED spotlight module (SLM) Gen2

Lexel LED downlight module (DLM)

Lexel LED spotlight module (SLM)

Fortimo LED strip system

| Module type | | | Suitable driver and cable combination | | | | | |
|-------------|---------------|---------------|---------------------------------------|---------------|---------------|-------|---------------|---------------|
| | Logistic code | European code | Driver | Logistic code | European code | Cable | Logistic code | European code |
| | 12NC | EOC | | 12NC | EOC | | 12NC | EOC |

Fortimo LED decorative modules

| 300 lumen | | | | | | | | |
|--|--------------|-----------------|---|--------------|-----------------|------------------------------------|--|--|
| Fortimo deco mini spot 300 827 10V | 929000663008 | 871829115835600 | Xitanium LED driver 10W/0.70A-14V DIM | 913710053666 | 871016306416130 | None (cables connected to modules) | | |
| Fortimo deco mini spot 300 840 10V | 929000662908 | 871829115837000 | Xitanium LED driver 30W/0.70A-42V DIM | 913710053866 | 871016306418530 | | | |
| Fortimo deco mini downlight 300 827 10V | 929000663108 | 871829115839400 | Xitanium LED dimmable driver 20/30W 42V (independent) | 913713220162 | 871016384331600 | | | |
| Fortimo deco mini downlight 300 840 10V | 929000663208 | 871829115841700 | | | | | | |
| Fortimo deco mini strip 300 40D 827 10V | 929000663408 | 871829115843100 | | | | | | |
| Fortimo deco mini strip 300 40D 840 10V | 929000669908 | 871829115845500 | | | | | | |
| Fortimo deco mini strip 300 100D 827 10V | 929000663308 | 871829115847900 | | | | | | |
| Fortimo deco mini strip 300 100D 840 10V | 929000670008 | 871829115849300 | | | | | | |

| Module type | | | Suitable driver and cable combination | | | | | |
|-------------|---------------|---------------|---------------------------------------|---------------|---------------|-------|---------------|---------------|
| | Logistic code | European code | Driver | Logistic code | European code | Cable | Logistic code | European code |
| | 12NC | EOC | | 12NC | EOC | | 12NC | EOC |

Fortimo LED disk modules

| 300 lumen | | | | | | | | |
|--|--------------|-----------------|-------------------------|--|--|-------------------------|--|--|
| Fortimo LED disk module 300/827 230V | 929000662803 | 871829116719800 | None, integrated system | | | None, integrated system | | |
| 800 lumen | | | | | | | | |
| Fortimo LED disk module 800/840 230V | 929000664608 | 871829115277400 | None, integrated system | | | None, integrated system | | |
| Fortimo LED disk module 800/927 230V W | 929000303501 | 871829111500700 | | | | | | |

| Module type | | | Suitable driver and cable combination | | | | | |
|---|---------------|-----------------|--|---------------|-----------------|--|---------------|-----------------|
| | Logistic code | European code | Driver | Logistic code | European code | Cable | Logistic code | European code |
| | 12NC | EOC | | 12NC | EOC | | 12NC | EOC |
| Fortimo LED downlight module (DLM) | | | | | | | | |
| 1100 lumen | | | | | | | | |
| Fortimo LED DLM 1100 10W/850 Gen3 | 929000660703 | 871829114388800 | Fortimo LED driver 1100-3000 (new) (successor of Fortimo LED driver 1100-2000) | 929000614403 | 872790092085700 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| Fortimo LED DLM 1100 11W/835 Gen3 | 929000660503 | 871829114386400 | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| Fortimo LED DLM 1100 11W/840 Gen3 | 929000660603 | 871829114387100 | Xitanium 45W 200-700mA 80V I 230V (successor of Fortimo driver 1100-2000/I) | 929000614503 | 872790092083300 | LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire | 929000615203 | 872790093129700 |
| Fortimo LED DLM 1100 12W/830 Gen3 | 929000660403 | 871829114385700 | Fortimo LED driver 1100-3000/TD | 929000465003 | 872790084297500 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | Fortimo LED driver 1100-3000 TD/I | 929000465203 | 872790086270600 | LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire | 929000615203 | 872790093129700 |
| | | | Xitanium 25W 0.3-0.7A 36V I 230V | 929000600203 | 872790090096500 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | Xitanium 25W 0.3-1A 36V TD/I 230V | 929000600403 | 872790091434400 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | Xitanium 25W/0.3-1A 36V TD/Is 230V | 929000485803 | 872790091435100 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 | | | |
| | | | Xitanium 25W 0.3-0.7A 36V TE/I 230V | 929000600303 | 872790090730800 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| 2000 lumen | | | | | | | | |
| Fortimo LED DLM 2000 20W/850 Gen3 | 929000661103 | 871829114392500 | Fortimo LED driver 1100-3000 (new) | 929000614403 | 872790092085700 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| Fortimo LED DLM 2000 22W/840 Gen3 | 929000661003 | 871829114391800 | (successor of Fortimo LED driver 1100-2000) | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| Fortimo LED DLM 2000 23W/835 Gen3 | 929000660903 | 871829114390100 | Xitanium 45W 200-700mA 80V I 230V (successor of Fortimo driver 1100-2000/I) | 929000614503 | 872790092083300 | LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire | 929000615203 | 872790093129700 |
| Fortimo LED DLM 2000 24W/830 Gen3 | 929000660803 | 871829114389500 | Fortimo LED driver 1100-3000/TD | 929000465003 | 872790084297500 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | Fortimo LED driver 1100-3000 TD/I | 929000465203 | 872790086270600 | LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire | 929000615203 | 872790093129700 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | Xitanium 50W 0.3-1A 62V 230V | 929000636303 | 871829113782500 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | Xitanium 50W SH 0.3-1A 62V I 230V | 929000617403 | 871829113780100 | LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire | 929000615203 | 872790093129700 |
| | | | | | | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | Xitanium 50W SH 0.3-1A 62V TD/TE I 230V | 929000661203 | 871829115712000 | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | | | | LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire | 929000615203 | 872790093129700 |

| 3000 lumen | | | | | | | | |
|-----------------------------------|--------------|-----------------|---|--------------|-----------------|---|--------------|-----------------|
| Fortimo LED DLM 3000 38W/850 Gen3 | 929000619103 | 871829114396300 | Fortimo LED driver 1100-3000 (new) (successor of Fortimo LED driver 1100-2000) | 929000614403 | 872790092085700 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| Fortimo LED DLM 3000 41W/840 Gen3 | 929000660303 | 871829114395600 | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| Fortimo LED DLM 3000 44W/830 Gen3 | 929000618903 | 871829114393200 | Xitanium 45W 200-700mA 80V I 230V (successor of Fortimo LED driver 1100-2000/I) | 929000614503 | 872790092083300 | LED DLM cable 60 cm / I 12V / 60 cm cable with earth wire | 929000615203 | 872790093129700 |
| Fortimo LED DLM 3000 44W/835 Gen3 | 929000619003 | 871829114394900 | FortimoLEDdriver1100-3000/TD | 929000465003 | 872790084297500 | Fortimo LED DLM cable 1100-2000 / 25 cm | 929000463103 | 872790080709700 |
| | | | Fortimo LED driver 1100-3000 TD/I | 929000465203 | 872790086270600 | LED DLM cable 60 cm / I 12V / 60 cm cable with earth wire | 929000484803 | 872790087989600 |
| | | | | | | | 929000615203 | 872790093129700 |

| Module type | Suitable driver and cable combination | | | | | | | | | |
|--|---------------------------------------|----------------------|---|-----------------------|----------------------|------------------------------------|-----------------------|----------------------|-----------------|--|
| | Logistic code 12NC | European code EOC | Driver | Logistic code 12NC | European code EOC | Cable | Logistic code 12NC | European code EOC | | |
| Fortimo LED downlight module (DLM) Food | | | | | | | | | | |
| 2000 lumen | | | | | | | | | | |
| Fortimo LED DLM 2000 50W/Food30 | 929000478003 | 872790086576900 | Fortimo LED DLM driver 2000 50W/Food 120-277V | 929000478103 | 872790086578300 | Fortimo LED DLM cable Food / 25 cm | 929000478203 | 872790086580600 | | |
| Fortimo LED DLM 2000 50W/Food40 | 929000478703 | 872790086575200 | | | | LED DLM cable 25 cm | 929000666103 | | | |
| | | | | | | LED DLM cable 60 cm | 929000484803 | | 872790087989600 | |
| Fortimo LED downlight module Twistable | | | | | | | | | | |
| 1100 lumen | | | | | | | | | | |
| Fortimo TDLM 1100 18W/840 230V | 929000499103 | 872790090534200 | Not applicable, power on board | | | Fortimo TDLM LH 1100 230V | 929000499503 | 872790092368100 | | |
| Fortimo TDLM 1100 20W/827 230V | 929000498903 | 872790090536600 | | | | | | | | |
| Fortimo TDLM 1100 20W/830 230V | 929000499003 | 872790090535900 | | | | | | | | |
| 2000 lumen | | | | | | | | | | |
| Fortimo TDLM 2000 32W/830 230V | 929000638003 | 871829114933000 | Not applicable, power on board | | | On request | | | | |
| Fortimo TDLM 2000 32W/840 230V | 929000638103 | 871829114934700 | | | | | | | | |

| Module type | | | Suitable driver and cable combination | | | | | |
|---|-----------------------|----------------------|---------------------------------------|-----------------------|----------------------|-----------------------------|-----------------------|----------------------|
| | Logistic code 12NC | European code EOC | Driver | Logistic code 12NC | European code EOC | Cable | Logistic code 12NC | European code EOC |
| Fortimo LED high brightness module (HBM) | | | | | | | | |
| 4000/6000 lumen, one module on one driver | | | | | | | | |
| Fortimo LED HBM 4000 35W/757 | 929000636603 | 871829114379600 | Xitanium 75W 0.35-0.7A GL Prog sXt | 929000702302 | 871829111887900 | Fortimo HBM cable 60 cm | 929000659803 | 871829114382600 |
| Fortimo LED HBM 4000 40W/641 | 929000636503 | 871829114378900 | | | | | | |
| Fortimo LED HBM 4000 45W/740 | 929000665003 | 871829116117200 | | | | | | |
| Fortimo LED HBM 6000 52W/757 | 929000636803 | 871829114381900 | | | | | | |
| Fortimo LED HBM 6000 59W/641 | 929000636703 | 871829114380200 | | | | | | |
| Fortimo LED HBM 6000 68W/740 | 929000665103 | 871829116119600 | | | | | | |
| 4000/6000 lumen, two modules on one driver | | | | | | | | |
| Fortimo LED HBM 4000 35W/757 x2 | 929000636603 | 871829114379600 | Xitanium 150W 0.35-0.7A GL Prog sXt | 929000702202 | 872790078351300 | Fortimo HBM Cable 60 cm, x2 | 929000659803 | 871829114382600 |
| Fortimo LED HBM 4000 40W/641 x2 | 929000636503 | 871829114378900 | | | | | | |
| Fortimo LED HBM 4000 45W/740 x2 | 929000665003 | 871829116117200 | | | | | | |
| Fortimo LED HBM 6000 52W/757 x2 | 929000636803 | 871829114381900 | | | | | | |
| Fortimo LED HBM 6000 59W/641 x2 | 929000636703 | 871829114380200 | | | | | | |
| Fortimo LED HBM 6000 68W/740 x2 | 929000665103 | 871829116119600 | | | | | | |
| Fortimo LED integrated spot module | | | | | | | | |
| 600 lumen | | | | | | | | |
| Fortimo integrated spot 600 827 15D 230V | 9290 006 94508 | 8718291 199564 00 | Non, integrated system | | | | | |
| Fortimo integrated spot 600 827 24D 230V | 9290 006 94608 | 8718291 199588 00 | | | | | | |
| Fortimo integrated spot 600 827 36D 230V | 9290 006 94708 | 8718291 199601 00 | | | | | | |
| Fortimo integrated spot 600 830 15D 230V | 9290 006 94808 | 8718291 199625 00 | | | | | | |
| Fortimo integrated spot 600 830 24D 230V | 9290 006 94908 | 8718291 199649 00 | | | | | | |
| Fortimo integrated spot 600 830 36D 230V | 9290 006 95008 | 8718291 199663 00 | | | | | | |
| Fortimo integrated spot 600 840 15D 230V | 9290 006 95108 | 8718291 199687 00 | | | | | | |
| Fortimo integrated spot 600 840 24D 230V | 9290 006 95208 | 8718291 199700 00 | | | | | | |
| Fortimo integrated spot 600 840 36D 230V | 9290 006 95308 | 8718291 199724 00 | | | | | | |

| Module type | | | Suitable driver and cable combination | | | | | |
|---|-----------------------|----------------------|---|-----------------------|----------------------|---|-----------------------|----------------------|
| | Logistic code 12NC | European code EOC | Driver | Logistic code 12NC | European code EOC | Cable | Logistic code 12NC | European code EOC |
| Fortimo LED linear light module (LLM) | | | | | | | | |
| 1100 lumen | | | | | | | | |
| Fortimo LED LLM 1100 13W/730 | 929000634903 | 871829111532800 | Xitanium 35W 0.20-0.70A 230V Otd | 929000634003 | 871829112003200 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS6 230V Otd | 929000634103 | 871829112004900 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS8 230V Otd | 929000634203 | 8718291 120056 00 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| Fortimo LED LLM 1100 11W/740 | 929000616103 | 871829112218000 | Xitanium 35W 0.20-0.70A 230V Otd | 929000634003 | 871829112003200 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS6 230V Otd | 929000634103 | 871829112004900 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS8 230V Otd | 929000634203 | 8718291 120056 00 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| Fortimo LED LLM 1100 12W/840 | 929000615703 | 871829111533500 | on request | | | | | |
| 1800 lumen | | | | | | | | |
| Fortimo LED LLM 1800 20W/730 | 929000635003 | 871829111534200 | Xitanium 35W 0.20-0.70A 230V Otd | 929000634003 | 871829112003200 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS6 230V Otd | 929000634103 | 871829112004900 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS8 230V Otd | 929000634203 | 871829112005600 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| Fortimo LED LLM 1800 18W/740 | 929000615903 | 871829112217300 | Xitanium 35W 0.20-0.70A 230V Otd | 929000634003 | 871829112003200 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS6 230V Otd | 929000634103 | 871829112004900 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| | | | Xitanium 35W 0.20-0.70A LS8 230V Otd | 929000634203 | 8718291 120056 00 | Fortimo LLM cable 25 cm | 929000483303 | 872790086714500 |
| Fortimo LED LLM 1800 20W/840 | 929000616003 | 871829112001800 | on request | | | | | |
| 3000 lumen | | | | | | | | |
| Fortimo LED LLM 3000 34W/730 | 929000611303 | 872790090365200 | Xitanium 75W 0.35-0.70A 1-10V 230V sXt + integrated cable | 913701217502 | 872790092567800 | No separate cable needed | | |
| Fortimo LED LLM 3000 33W/740 | 929000611403 | 872790090366900 | Xitanium 75W 0.35-0.7A GL Prog sXt | 929000702302 | 871829111887900 | No cable released; need 6 pins to flying leads | | |
| | | | Xitanium 75W 0.35-0.70A 1-10V 230V sXt + | 913701217502 | 872790092567800 | No separate cable needed | | |
| 4500 lumen | | | | | | | | |
| Fortimo LED LLM 4500 53W/730 | 929000611103 | 872790090363800 | Xitanium 75W 0.35-0.70A 1-10V 230V sXt + integrated | 913701217502 | 872790092567800 | No separate cable needed | | |
| | | | Xitanium 75W 0.35-0.7A GL Prog sXt | 929000702302 | 871829111887900 | No cable released; need 6 pins to flying leads | | |
| Fortimo LED LLM 4500 50W/740 | 929000611203 | 872790090364500 | Xitanium 75W 0.35-0.70A 1-10V 230V sXt + integrated | 913701217502 | 872790092567800 | No separate cable needed | | |
| | | | Xitanium 75W 0.35-0.7A GL Prog sXt | 929000702302 | 871829111887900 | No cable released; need 6 pins to flying leads | | |
| 1800 lumen (two modules on one driver) | | | | | | | | |
| Fortimo LED LLM 1800 20W/730 (2x) | 929000635003 | 871829111534200 | Xitanium 75W 0.35-0.7A GL Prog sXt | 929000702302 | 871829111887900 | No cable released; need 5 pins to flying leads x2 | | |
| Fortimo LED LLM 1800 18W/740 (2x) | 929000615903 | 871829112217300 | Xitanium 75W 0.35-0.7A GL Prog sXt | 929000702302 | 871829111887900 | No cable released; need 5 pins to flying leads x2 | | |
| 3000 lumen (two modules on one driver) | | | | | | | | |
| Fortimo LED LLM 3000 34W/730 (2x) | 929000611303 | 872790090365200 | Xitanium 150W 0.35-0.7A GL Prog sXt | 929000702202 | 8727900783513 00 | No cable released; need 6 pins to flying leads x2 | | |
| Fortimo LED LLM 3000 33W/740 (2x) | 929000611403 | 872790090366900 | Xitanium 150W 0.35-0.7A GL Prog sXt | 929000702202 | 8727900783513 00 | No cable released; need 6 pins to flying leads x2 | | |
| 4500 lumen (two modules on one driver) | | | | | | | | |
| Fortimo LED LLM 4500 53W/730 (2x) | 929000611103 | 872790090363800 | Xitanium 150W 0.35-0.7A GL Prog sXt | 929000702202 | 8727900783513 00 | No cable released; need 6 pins to flying leads x2 | | |
| Fortimo LED LLM 4500 50W/740 (2x) | 929000611203 | 872790090364500 | Xitanium 150W 0.35-0.7A GL Prog sXt | 929000702202 | 8727900783513 00 | No cable released; need 6 pins to flying leads x2 | | |

| Module type | | | Suitable driver and cable combination | | | | | |
|--|---------------|-----------------|--|---------------|-----------------|--|---------------|-----------------|
| | Logistic code | European code | Driver | Logistic code | European code | Cable | Logistic code | European code |
| | 12NC | EOC | | 12NC | EOC | | 12NC | EOC |
| Fortimo LED linear light module (LLM) Solar | | | | | | | | |
| 1800 lumen | | | | | | | | |
| Fortimo LED LLM 1800 20W/730 | 929000635003 | 871829111534200 | Xitanium 40W 0.2-0.7A LS 12-24VDC (Solar driver) | 929000611903 | 872790092559300 | 50cm | 929000615103 | 872790093033700 |
| Fortimo LED LLM 1800 18W/740 | 929000615903 | 871829112217300 | | | | | | |
| Fortimo LED LLM 1800 20W/840 | 929000616003 | 871829112001800 | | | | | | |
| 3000 lumen | | | | | | | | |
| Fortimo LED LLM 3000 34W/730 | 929000611303 | 872790090365200 | Xitanium 40W 0.2-0.7A LS 12-24VDC (Solar driver) | 929000611903 | 872790092559300 | 50cm | 929000614903 | 872790093031300 |
| Fortimo LED LLM 3000 33W/740 | 929000611403 | 872790090366900 | | | | | | |
| 4500 lumen | | | | | | | | |
| Fortimo LED LLM 4500 53W/730 DS | 929000612103 | 872790092032100 | Xitanium 70W 0.2-0.7A LS 12-24VDC (Solar driver) | 929000612003 | 872790092560900 | Cable Fortimo Solar LLM driver 4500lm 50929000615003 | | 872790093032000 |
| Fortimo LED LLM 4500 48W/740 DS | 929000612203 | 872790092033800 | | | | | | |

| Module type | Suitable driver and cable combination | | | | | | | |
|--|---------------------------------------|-----------------|---|---------------|-----------------|-----------------------------------|---------------|-----------------|
| | Logistic code | European code | Driver | Logistic code | European code | Cable | Logistic code | European code |
| | 12NC | EOC | | 12NC | EOC | | 12NC | EOC |
| Fortimo LED spotlight module (SLM) - Gen1 | | | | | | | | |
| 800/1100 lumen - Gen1 | | | | | | | | |
| Fortimo LED SLM 800 10W/835 | 929000621503 | 871829111866400 | Xitanium 25W 0.3-0.7A 36V I 230V | 929000600203 | 872790090096500 | Fortimo LED SLM cable 25 cm | 929000614703 | 872790092152600 |
| Fortimo LED SLM 800 10W/840 | 929000621603 | 871829111867100 | Xitanium 25W 0.3-0.7A 36V TE/I 230V | 929000600303 | 872790090730800 | Fortimo LD SLM cable 60 cm | 929000619203 | 872790095423400 |
| Fortimo LED SLM 800 11W/830 | 929000621403 | 871829111865700 | Xitanium 25W 0.3-1A 36V TD/I 230V | 929000600403 | 872790091434400 | Fortimo LED SLM cable 60 cm, 12V | 929000632903 | 872790095424100 |
| Fortimo LED SLM 1100 15W/840 | 929000612903 | 872790091410800 | Xitanium 25W 0.3-1A 36V TD/Is 230V | 929000485803 | 872790091435100 | | | |
| Fortimo LED SLM 1100 17W/830 | 929000611503 | 872790091406100 | Fortimo LED Driver 1100-3000 | 929000614403 | 872790092085700 | | | |
| Fortimo LED SLM 1100 17W/835 | 929000612703 | 872790091408500 | Fortimo LED Driver 1100-3000/TD | 929000465003 | 872790084297500 | | | |
| | | | Fortimo LED Driver 1100-3000/I | 929000465103 | 872790082522000 | | | |
| | | | Fortimo LED Driver 1100-3000/TDI | 929000465203 | 872790086270600 | | | |
| | | | Xitanium 45W 200-700mA 80V I 230V | 929000614503 | 872790092083300 | | | |
| 1500/2000 lumen - Gen1 | | | | | | | | |
| Fortimo LED SLM 1500 19W/840 | 929000621903 | 871829111864000 | Xitanium 50W/s 0.3-1A 62V 230V | 929000636403 | 871829113781800 | Fortimo LED SLM cable 25 cm | 929000614703 | 872790092152600 |
| Fortimo LED SLM 1500 20W/830 | 929000621703 | 871829111862600 | Xitanium 50W 0.3-1A 62V 230V | 929000636303 | 871829113782500 | Fortimo LED SLM cable 60 cm | 929000619203 | 872790095423400 |
| Fortimo LED SLM 1500 20W/835 | 929000621803 | 871829111863300 | Xitanium 50W 0.3-1A 62V TD/TE 230V | 929000661203 | 871829115712000 | Fortimo LED SLM cable 60 cm, 12 V | 929000632903 | 872790095424100 |
| Fortimo LED SLM 2000 29W/840 | 929000613003 | 872790091411500 | Xitanium 50W SH 0.3-1A 62V I 230V | 929000617403 | 871829113780100 | | | |
| Fortimo LED SLM 2000 32W/830 | 929000611603 | 872790091407800 | Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V | 929000617103 | 871829111947000 | | | |
| Fortimo LED SLM 2000 32W/835 | 929000612803 | 872790091409200 | Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V | 929000617203 | 871829111948700 | | | |
| | | | Fortimo LED Driver 1100-3000 | 929000614403 | 872790092085700 | | | |
| | | | Fortimo LED Driver 1100-3000/TD | 929000465003 | 872790084297500 | | | |
| | | | Fortimo LED Driver 1100-3000/I | 929000465103 | 872790082522000 | | | |
| | | | Fortimo LED Driver 1100-3000/TDI | 929000465203 | 872790086270600 | | | |
| | | | Xitanium 45W 200-700mA 80V I 230V | 929000614503 | 872790092083300 | | | |
| 3000 lumen - Gen1 | | | | | | | | |
| Fortimo LED SLM 3000 38W/840 | 929000635903 | 871829111861900 | Xitanium 50W/s 0.3-1A 62V 230V | 929000636403 | 871829113781800 | Fortimo LED SLM cable 25 cm | 929000614703 | 872790092152600 |
| Fortimo LED SLM 3000 43W/830 | 929000635703 | 871829111859600 | Xitanium 50W 0.3-1A 62V 230V | 929000636303 | 871829113782500 | Fortimo LED SLM cable 60 cm | 929000619203 | 872790095423400 |
| Fortimo LED SLM 3000 41W/835 | 929000635803 | 871829111860200 | Xitanium 50W 0.3-1A 62V TD/TE 230V | 929000661203 | 871829115712000 | Fortimo LED SLM cable 60 cm, 12 V | 929000632903 | 872790095424100 |
| | | | Xitanium 50W SH 0.3-1A 62V I 230V | 929000617403 | 871829113780100 | | | |
| | | | Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V | 929000617103 | 871829111947000 | | | |
| | | | Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V | 929000617203 | 871829111948700 | | | |

| Module type | Suitable driver and cable combination | | | | | | | |
|--|---------------------------------------|------------------|---|---------------|-----------------|-----------------------------------|---------------|-----------------|
| | Logistic code | European code | Driver | Logistic code | European code | Cable | Logistic code | European code |
| | 12NC | EOC | | 12NC | EOC | | 12NC | EOC |
| Fortimo LED spotlight module (SLM) - Gen2 | | | | | | | | |
| 2000 lumen - Gen2 | | | | | | | | |
| Fortimo LED SLM 2000 25W/827 L19 G2 | 9290 006 75403 | 871829118627400 | Xitanium 50W/s 0.3-1A 62V 230V | 929000636403 | 871829113781800 | Fortimo LED SLM cable 25 cm | 929000614703 | 872790092152600 |
| Fortimo LED SLM 2000 23W/830 L19 G2 | 9290 006 75803 | 871829118631100 | Xitanium 50W 0.3-1A 62V 230V | 929000636303 | 871829113782500 | Fortimo LED SLM cable 60 cm | 929000619203 | 872790095423400 |
| Fortimo LED SLM 2000 22W/835 L19 G2 | 9290 006 76203 | 871829118638000 | Xitanium 50W 0.3-1A 62V TD/TE 230V | 929000661203 | 871829115712000 | Fortimo LED SLM cable 60 cm, 12 V | 929000632903 | 872790095424100 |
| Fortimo LED SLM 2000 20W/840 L19 G2 | 9290 006 76403 | 871829118678600 | Xitanium 50W SH 0.3-1A 62V I 230V | 929000617403 | 871829113780100 | | | |
| | | | Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V | 929000617103 | 871829111947000 | | | |
| | | | Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V | 929000617203 | 871829111948700 | | | |
| | | | Fortimo LED Driver 1100-3000 | 929000614403 | 872790092085700 | | | |
| | | | Fortimo LED Driver 1100-3000/TD | 929000465003 | 872790084297500 | | | |
| | | | Fortimo LED Driver 1100-3000/I | 929000465103 | 872790082522000 | | | |
| | | | Fortimo LED Driver 1100-3000/TDI | 929000465203 | 872790086270600 | | | |
| | | | Xitanium 45W 200-700mA 80V I 230V | 929000614503 | 872790092083300 | | | |
| 2000/3000 lumen - Gen2 | | | | | | | | |
| Fortimo LED SLM 2000 34W/927 L19 G2 | 9290 006 75603 | 87182911 8629800 | Xitanium 50W/s 0.3-1A 62V 230V | 929000636403 | 871829113781800 | Fortimo LED SLM cable 25 cm | 929000614703 | 872790092152600 |
| Fortimo LED SLM 2000 31W/930 L19 G2 | 9290 006 76003 | 87182911 8636600 | Xitanium 50W 0.3-1A 62V 230V | 929000636303 | 871829113782500 | Fortimo LED SLM cable 60 cm | 929000619203 | 872790095423400 |
| Fortimo LED SLM 3000 42W/827 L19 G2 | 9290 006 76503 | 87182911 8680900 | Xitanium 50W 0.3-1A 62V TD/TE 230V | 929000661203 | 871829115712000 | Fortimo LED SLM cable 60 cm, 12 V | 929000632903 | 872790095424100 |
| Fortimo LED SLM 3000 39W/830 L19 G2 | 9290 006 76903 | 87182911 8684700 | Xitanium 50W SH 0.3-1A 62V I 230V | 929000617403 | 871829113780100 | | | |
| Fortimo LED SLM 3000 40W/835 L19 G2 | 9290 006 77303 | 87182911 8682300 | Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V | 929000617103 | 871829111947000 | | | |
| Fortimo LED SLM 3000 36W/840 L19 G2 | 9290 006 77503 | 87182911 8686100 | Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V | 929000617203 | 871829111948700 | | | |

| Module type | | | Suitable driver and cable combination | | | | | |
|---|---------------|-----------------|---------------------------------------|---------------|-----------------|-------------------------------------|---------------|-----------------|
| | Logistic code | European code | Driver | Logistic code | European code | Cable | Logistic code | European code |
| | 12NC | EOC | | 12NC | EOC | | 12NC | EOC |
| Lexel LED downlight module (DLM) | | | | | | | | |
| 1100 lumen | | | | | | | | |
| Lexel LED DLM module 1100 2700-6500 | 929000463203 | 872790081322700 | Lexel LED DLM driver 1100 DALI/DMX | 929000484203 | 872790088575000 | Lexel LED DLM cable 1100 | 929000463503 | 872790081324100 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | | | | LED DLM cable 60cm /l 12V | 929000615203 | 872790093129700 |
| 2000 lumen | | | | | | | | |
| Lexel LED DLM module 2000 2700-6500 | 929000659903 | 871829113935500 | Lexel LED DLM driver 1100 DALI/DMX | 929000484203 | 872790088575000 | Lexel LED DLM cable 1100 | 929000463503 | 872790081324100 |
| | | | | | | LED DLM cable 60 cm | 929000484803 | 872790087989600 |
| | | | | | | LED DLM cable 60cm /l 12V | 929000615203 | 872790093129700 |
| Lexel LED spotlight module (SLM) | | | | | | | | |
| 800 lumen | | | | | | | | |
| Lexel LED SLM module 800 25W/RGB | 929000620303 | 872790095416600 | Lexel LED driver 25W - DMX | 929000632703 | 871829112509900 | Lexel LED SLM cable 25 cm or | 929000620403 | 872790095417300 |
| | | | | | | Lexel LED SLM cable 60 cm and | 929000633203 | 872790095420300 |
| | | | | | | Lexel LED SLM DMX/4B cable 60 cm FL | 929000661303 | 871829113937900 |
| | | | Lexel LED driver 25W - DALI | 929000620503 | 871829112508200 | Lexel LED SLM cable 25 cm or | 929000620403 | 872790095417300 |
| | | | | | | Lexel LED SLM cable 60 cm and | 929000633203 | 872790095420300 |
| | | | Lexel LED driver 25W - 4B | 929000632803 | 871829112510500 | Lexel LED SLM cable 25 cm or | 929000620403 | 872790095417300 |
| | | | | | | Lexel LED SLM cable 60 cm and | 929000633203 | 872790095420300 |
| | | | | | | Lexel LED SLM DMX/4B cable 60 cm FL | 929000661303 | 871829113937900 |
| 1100 lumen | | | | | | | | |
| Lexel LED SLM module 1100 22W/8TV | 929000620203 | 872790095415900 | Lexel LED driver 25W - DMX TW | 929000659703 | 871829114017700 | Lexel LED SLM cable 25 cm or | 929000620403 | 872790095417300 |
| | | | | | | Lexel LED SLM cable 60 cm and | 929000633203 | 872790095420300 |
| | | | | | | Lexel LED SLM DMX/4B cable 60 cm FL | 929000661303 | 871829113937900 |
| | | | Lexel LED driver 25W - DALI | 929000620503 | 871829112508200 | Lexel LED SLM cable 25 cm or | 929000620403 | 872790095417300 |
| | | | | | | Lexel LED SLM cable 60 cm | 929000633203 | 872790095420300 |
| | | | Lexel LED driver 25W - 4B | 929000632803 | 871829112510500 | Lexel LED SLM cable 25 cm or | 929000620403 | 872790095417300 |
| | | | | | | Lexel LED SLM cable 60 cm and | 929000633203 | 872790095420300 |
| | | | | | | Lexel LED SLM DMX/4B cable 60 cm FL | 929000661303 | 871829113937900 |

| Module type | | | | Suitable driver and cable combination | | | | | |
|-------------|----------|----------|---------------|---------------------------------------|----------|----------|------------------------|----------|----------|
| | Logistic | European | Nr. of strips | Driver | Logistic | European | Cable driver to module | Logistic | European |
| | code | code | | | code | code | | code | code |
| | 12NC | EOC | | | 12NC | EOC | | 12NC | EOC |

Fortimo LED strip system

| 630 lumen | | | | | | | | | |
|-----------------------------------|----------------|-------------------|----|-------------------------------------|----------------|-------------------|------------------------------|----------------|-------------------|
| Fortimo LED Strip 280mm 630lm 830 | 9290 006 68803 | 8718291161738 00 | 5 | Xitanium 75W 200mA 200V TD 230V | 929000661803 | 871829115255200 | Fortimo LED strip cable 60cm | 9290 006 37703 | 87182911 51456 00 |
| | | | 6 | Xitanium 75W 240mA 200V TD 230V | 929000661903 | 871829115256900 | | | |
| | | | 7 | Xitanium 75W 280mA 200V TD 230V | 929000662003 | 871829115257600 | | | |
| | | | 8 | Xitanium 75W 320mA 200V TD 230V | 929000662103 | 871829115258300 | | | |
| | | | 9 | Xitanium 75W 360mA 200V TD 230V | 929000662203 | 871829115259000 | | | |
| | | | 10 | Xitanium 75W 0.15-0.4A 200V TD 230V | 9290 006 70403 | 87182911 68188 00 | | | |
| Fortimo LED Strip 280mm 630lm 840 | 9290 006 37603 | 87182911 50008 00 | 5 | Xitanium 75W 200mA 200V TD 230V | 929000661803 | 871829115255200 | Fortimo LED strip cable 60cm | 9290 006 37703 | 87182911 51456 00 |
| | | | 6 | Xitanium 75W 240mA 200V TD 230V | 929000661903 | 871829115256900 | | | |
| | | | 7 | Xitanium 75W 280mA 200V TD 230V | 929000662003 | 871829115257600 | | | |
| | | | 8 | Xitanium 75W 320mA 200V TD 230V | 929000662103 | 871829115258300 | | | |
| | | | 9 | Xitanium 75W 360mA 200V TD 230V | 929000662203 | 871829115259000 | | | |
| | | | 10 | Xitanium 75W 0.15-0.4A 200V TD 230V | 9290 006 70403 | 87182911 68188 00 | | | |
| Fortimo LED Strip 280mm 630lm 865 | 9290 006 69003 | 8718291161783 00 | 5 | Xitanium 75W 200mA 200V TD 230V | 929000661803 | 871829115255200 | Fortimo LED strip cable 60cm | 9290 006 37703 | 87182911 51456 00 |
| | | | 6 | Xitanium 75W 240mA 200V TD 230V | 929000661903 | 871829115256900 | | | |
| | | | 7 | Xitanium 75W 280mA 200V TD 230V | 929000662003 | 871829115257600 | | | |
| | | | 8 | Xitanium 75W 320mA 200V TD 230V | 929000662103 | 871829115258300 | | | |
| | | | 9 | Xitanium 75W 360mA 200V TD 230V | 929000662203 | 871829115259000 | | | |
| | | | 10 | Xitanium 75W 0.15-0.4A 200V TD 230V | 9290 006 70403 | 87182911 68188 00 | | | |



©2011 Koninklijke Philips Electronics N.V.
All rights reserved. Data subject to change.

www.philips.com/fortimo
www.philips.com/oem