

6

5

4

3

2

1

**MATERIAL AND FINISH:**

Insulator: PBT, Glass filled Polyester, UL 94V-0 rated. Color black

Contact: Phosphor Bronze, gold flash plated

**ELECTRICAL SPECIFICATIONS:**




Rated current: 3A

Insulation resistance: 1000 Mohm min.

Dielectric withstanding voltage: 650VAC for one minute

Contact resistance: 20 mohm max

RoHS  
COMPLIANT



D

D

C

C

B

B

A

A

REVISIONS	CHNG	CHK	APPR
	REV	DATE	CHANGE

TOLERANCE UNLESS OTHERWISE SPECIFIED		
X	±	1
X.X	±	0.4
X.XX	±	0.20

**Power Dynamics, Inc.**  
 Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076  
**PART: 2 POSITION, 2.54mm PITCH  
 MINI JUMPER**

DRAWN BY	DT	DATE:	3/14/00
CHECK BY	JJ	DATE:	3/14/00
APPR BY	PB	DATE:	3/14/00

PART #:		<b>PD-JPS-1-O</b>	SHEET
SIZE:		A	1 of 1
SCALE:		NTS	REV:

ALL DIMENSIONS FOR REFERENCE ONLY  
DIMENSIONS ARE IN MILLIMETERS

6

5

4

3

2

1