





RMX-9000-1A

PART NO.

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES,
 ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED
 WITHOUT WRITTEN PERMISSION FROM RF INDUSTRIES.
 ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

ALL DIMENSIONS ARE REFERENCE ONLY

REV	DESCRIPTION	DWN	DATE	APPROVED
A	ENGINEERING RELEASE	CZS	3/31/99	R. RICE
B	CHANGE DRAWING # FROM 9152A	CZS	8/1/00	JDMc



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
 FOR RG-178, 178A, 178B, 178BB, 196, 196A/U

CRIMPED FERRULE
 HEX CRIMP SIZE .130*
 RECOMMENDED
 CABLE STRIPPING DIM'S

1	BODY	1	BRASS	GOLD, 3 MICRO	008974
2	INSULATOR	1	PTFE		
3	FERRULE STUD	1	BRASS	GOLD, 3 MICRO	
4	CONTACT	1	BRASS	GOLD, 30 MICRO	
5	RETAINING RING	1	Be, Cu	GOLD, 3 MICRO	
6	FERRULE	1	COPPER	GOLD, 3 MICRO	
7					
8					
9					
10					
11					
12					
13					
14					
#	DESCRIPTION	QTY	MATRL	FINISH	

UNLESS OTHERWISE SPECIFIED:
 1. REMOVE ALL BURRS
 2. BREAK ALL CORNERS & EDGES .005 R. MAX.
 3. CHAMFER 1ST & LAST THREADS 45°
 4. SURFACE ROUGHNESS 63 FINISH MIL-STD-10
 5. DIAMETERS ON COMMON CENTERS TO BE CONCENTRIC WITHIN .002 T.I.R.
 6. ALL DIMENSIONS ARE AFTER PLATING.

DIMENSIONS ARE IN INCHES
 AND [MILLIMETERS]
 UNLESS OTHERWISE NOTED
 TOLERANCES ARE:
 DECIMALS .XXX±.003 [.08]
 .XX±.005 [.13]
 DIAMETER .XXX±.001 [.03]
 .XX±.003 [.08]

DRAWN	8/1/00	DATE
CHECKED	AWM 8-2-00	
ORJ DRAWN	3/31/99	
C. ZUNIGA		
APPROVALS		

RF connectors
 DIVISION OF RF INDUSTRIES, LTD.
 7610 MIRAMAR RD
 SAN DIEGO, CA 92126
 (858) 549-6340
 (858) 549-6345 FAX

MMCX CRIMP PLUG

SIZE	CABLE GROUP	DWG NO.	REV
A	A	RMX-9000-1A	B
SCALE:	NTS	CAD FILE	OUTLINE
SHEET	1	OF	1