

CR2025 MFR

3V Lithium Battery


Technical Data Sheet

Specifications

Chemical System	Li / MnO ₂
Nominal Voltage	3 V
Rated Capacity	165 mAh
Standard Discharge Current	0.3 mA
Max. Cont. Discharge Current	3.0 mA
Average Weight	2.5 g
Temperature Range	-30 - +60 °C
Self Discharge at 23°C	< 1% / year


Dimensions

(According to IEC 60086)




Performance


Discharge performance at 23°C




Discharge performance at 23°C



Temperature performance Load 12kΩ



Cell capacity at various loads



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.

Rev. CR2025MFR.03 / 12.06