

### CHARACTERISTICS

Weight: 0,77 Kg / 1,7 Lb  
 Housing in ZAMAK  
 Impeller in plastic UL 94 V-0  
 L-10 life expectancy at 40°C: 80.000 hours  
 Operating temperature range: -10 / +55 °C  
 Storage temperature: -40 / +70°C  
 Connection: Terminals  
 Brushless DC motor  
 Integrated circuit



### OPTIONS

Speed sensor  
 Alarm  
 Other IP levels  
 Flying leads connection  
 Salt spray protection  
 Shocks and vibrations protection  
 Marine application  
 Wide temperature range  
 Other voltages  
 Others speeds

Part Number	Voltage V	Voltage range	Airflow		Pressure		Nominal speed RPM	Noise level LP dBA	Nominal current mA	power W
			l/s	CFM	mm H <sub>2</sub> o	inch H <sub>2</sub> o				
121DH2TM11200	24	19V-28V	105,0	222,60	22,5	0,89	4000	62	958	23
148DH1TM11000	12	9V-15V	110,0	233,20	12,5	0,49	3100	57	1080	13
2	24	19V-28V	112,0	237,44	12	0,47	3100	58	683	16,4
4	48	40V-57V	112,0	237,44	12	0,47	3100	58	340	16,3
9	110	76V-140V	112,0	237,44	12	0,47	3100	58	122	13,4
121DW2TM11200	24	19V-26,5V	120,0	254,40	32,51	1,28	4650	66	1250	30
9	28	19V-31V	120,0	254,40	32,5	1,28	4650	66	1071	30

