

1. Model : CL05C3R3CB5NNNC

2. Description

Part no.	CL05C3R3CB5NNNC
Size (inch / mm)	0402/1005
Thickness (mm)	0.5
Temperature characteristics	C0G
Capacitance	3.3 pF
Capacitance tolerance (%)	± 0.25pF
Voltage (V)	50

3. Frequency characteristics

Network Analyzer, 0.5Vrms, 1MHz to 20GHz

