

1. Model : CL10C1R8CB8NNNC

2. Description

Part no.	CL10C1R8CB8NNNC
Size (inch / mm)	0603/1608
Thickness (mm)	0.8
Temperature characteristics	C0G
Capacitance	1.8pF
Capacitance tolerance (%)	± 0.25pF
Voltage (V)	50

3. Frequency characteristics

Network Analyzer, 0.5Vrms, 1MHz to 20GHz

