

## 1. Model : CL31C3R9BBCNNNC

## 2. Description

Part no.	CL31C3R9BBCNNNC
Size (inch / mm)	1206/3216
Thickness (mm)	0.85
Temperature characteristics	C0G
Capacitance	3.9pF
Capacitance tolerance (%)	± 0.1pF
Voltage (V)	50

## 3. Frequency characteristics

Network Analyzer, 0.5Vrms, 1MHz to 20GHz

