

## 1. Model : CL31C561JBCNNNC

## 2. Description

Part no.	CL31C561JBCNNNC
Size (inch / mm)	1206/3216
Thickness (mm)	0.85
Temperature characteristics	C0G
Capacitance	560pF
Capacitance tolerance (%)	± 5 %
Voltage (V)	50

## 3. Frequency characteristics

Network Analyzer, 0.5Vrms, 1MHz to 20GHz

