

SULLINS

Product Number: EBC50DRTN

Product Description

- * PBT/Phosphor Bronze
Operating Temperature:
-65°C to +125°C
Processing Temperature: 260° FOR 10 sec. MAX
- * Contact Surface: .000010" Gold;
- * Termination: .000100" Pure Tin, Matte
- * .100" [2.54mm]
- * 98 Total Contacts
- * Dual Readout
- * .140"[3.56mm] Row Spacing;
.200"[5.08mm] Long Dip Solder
- * No Mounting

SPECIFICATIONS

- * Accommodates .062" \pm .008" [1.57 \pm .20] PC Board
- * 3 AMP Current Rating Per Contact
- * 30 Milli OHM Maximum at Rated Current
- * Molded-in Key available In-between or in Contact Key