



■ 40x40x20



Model	Bearing ● VAPO	Rating Voltage (VDC)	Power Current (mA)
MB40200V1-0000-A99	●	5	190
MB40200V2-0000-A99	●	5	123
MB40200V3-0000-A99	●	5	81
MB40201VX-0000-A99	●	12	115
MB40201V1-0000-A99	●	12	70
MB40201V2-0000-A99	●	12	50
MB40201V3-0000-A99	●	12	40
MB40202VX-0000-A99	●	24	64
MB40202V1-0000-A99	●	24	50
MB40202V2-0000-A99	●	24	33



Model	Bearing ○ SLEEVE	(VDC)	(mA)	(WATTS)	(RPM)	(CFM)	(Inch-H2O)	(dBA)	(g)
EB40200S1-0000-999	○	5	218	1.09	7200	8.9	0.21	25.5	30.0
EB40200S2-0000-999	○	5	140	0.70	6200	7.7	0.16	21.0	30.0
EB40200S3-0000-999	○	5	100	0.50	5200	6.3	0.11	18.0	30.0
EB40201SX-0000-999	○	12	120	1.44	8200	10.8	0.27	27.5	31.0
EB40201S1-0000-999	○	12	90	1.08	7200	8.9	0.21	25.5	31.0
EB40201S2-0000-999	○	12	63	0.76	6200	7.7	0.16	21.0	31.0
EB40201S3-0000-999	○	12	45	0.54	5200	6.3	0.11	18.0	31.0
EB40202S1-0000-999	○	24	54	1.30	7200	8.9	0.21	25.5	31.0
EB40202S2-0000-999	○	24	33	0.80	6200	7.7	0.16	21.0	31.0

* If you need special specification. Please contact Sunon sales.

* Specifications are subject to change without notice. Specifications in this catalog are for reference. More Sunon products information please visit SUNON web site at <http://www.sunon.com>.