



■ 60x60x15



Model	Bearing ● VAPO	(VDC)	(mA)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
ME60151V1-0000-A99	●	12	160	1.92	5400	25.2	0.15	36.2	30.5
ME60151V2-0000-A99	●	12	140	1.68	4700	21.9	0.12	32.5	30.5
ME60151V3-0000-A99	●	12	75	0.90	3900	18.1	0.08	28.2	30.5
ME60152V1-0000-A99	●	24	100	2.40	5400	25.2	0.15	36.2	30.5
ME60152V2-0000-A99	●	24	85	2.04	4700	21.9	0.12	32.5	30.5

* If you need special specification. Please contact Sunon sales.

* Specifications are subject to change without notice. Specifications in this catalog are for reference. More Sunon products information please visit SUNON web site at <http://www.sunon.com>.