



120X120X38 mm

93~138 CFM



	Bearing	Rating Voltage (VDC)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)	Curve
	● VAPO									
MEC0381V1-0000-A99	●	12	0.845	10.1	3100	138	0.36	48	218	1
MEC0381V2-0000-A99	●	12	0.5	6.0	2600	116	0.26	44	218	2
MEC0381V3-0000-A99	●	12	0.27	3.2	2100	93	0.18	37	218	3
MEC0382V1-0000-A99	●	24	0.415	10.0	3100	138	0.36	48	218	1
MEC0382V2-0000-A99	●	24	0.23	5.5	2600	116	0.26	44	218	2
MEC0382V3-0000-A99	●	24	0.135	3.2	2100	93	0.18	37	218	3
MEC0384V1-0000-A99	●	48	0.245	11.8	3100	138	0.36	48	218	1
MEC0384V2-0000-A99	●	48	0.14	6.7	2600	116	0.26	44	218	2
MEC0384V3-0000-A99	●	48	0.075	3.6	2100	93	0.18	37	218	3

Model		(VDC)	(AMP)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)	Curve
EEC0381B1-0000-A99	☉	12	0.8	9.6	3100	138	0.36	48	214	1
EEC0381B2-0000-A99	☉	12	0.48	5.8	2600	116	0.26	44	214	2
EEC0381B3-0000-A99	☉	12	0.255	3.1	2100	93	0.18	37	214	3
EEC0382B1-0000-A99	☉	24	0.4	9.6	3100	138	0.36	48	214	1
EEC0382B2-0000-A99	☉	24	0.215	5.2	2600	116	0.26	44	214	2
EEC0382B3-0000-A99	☉	24	0.13	3.1	2100	93	0.18	37	214	3
EEC0384B1-0000-A99	☉	48	0.215	10.3	3100	138	0.36	48	214	1
EEC0384B2-0000-A99	☉	48	0.125	6.0	2600	116	0.26	44	214	2
EEC0384B3-0000-A99	☉	48	0.07	3.4	2100	93	0.18	37	214	3



*All model could be customized. Please contact with Sunon Sales.

*Specifications subject to change without notice. Please Visit SUNON web site at <http://www.sunon.com> for update information.