GBJ25005 thru GBJ2510

GLASS PASSIVATED BRIDGE RECTIFIERS

REVERSE VOLTAGE - **50** to **1000**Volts
FORWARD CURRENT - **25** Amperes

FEATURES

- Rating to 1000V PRV
- Ideal for printed circuit board
- Low forward voltage drop,high current capability
- Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- The plastic material has UL flammability classification 94V-0

GBJ



Dimensions in inches and (milimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25℃ ambient temperature unless otherwise specified.

Single phase, half wave ,60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	GBJ 25005	GBJ 2501	GBJ 2502	GBJ 2504	GBJ 2506	GBJ 2508	GBJ 2510	UNIT
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward (with heatsink Note 2) Rectified Current @ T_C=100℃ (without heatsink)	$I_{(AV)}$	25.0 4.2							A
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	I_{FSM}	350							A
Maximum Forward Voltage at 12.5A DC	V_F	1.0							V
Maximum DC Reverse Current @ T_J=25℃ at Rated DC Blocking Voltage @ T_J=125℃	I_R	10.0 500							μA
I^2t Rating for Fusing (t<8.3ms)	I^2t	508							A^2s
Typical Junction Capacitance Per Element (Note1)	C_J	85							pF
Typical Thermal Resistance	$R_{\theta JC}$	0.6							℃/W
Operating Temperature Range	T_J	-55 to +150							℃
Storage Temperature Range	T_{STG}	-55 to +150							℃

NOTES: 1.Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

2.Device mounted on 300mm*300mm*1.6mm Cu plate heatsink.

3.The typical data above is for reference only(典型值仅供参考).

RATING AND CHARACTERTIC CURVES
GBJ25005 thru GBJ2510

FIG.1-FORWARD CURRENT DERATING CURVE



FIG.2-MAXMUN NON-REPETITIVE SURGE CURRENT



FIG.3-TYPICAL JUNCTION CAPACITANCE



FIG.4-TYPICAL FORWARD CHARACTERISTICS



FIG.5-TYPICAL REVERSE CHARACTERISTICS



The curve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!