



# Temperature compensated chip attenuators

P \* V series

## Features

- For simplifying temperature drift compensation of GaAs high frequency amplifiers
- Excellent high frequency characteristics

## Applications

- Base station and others



\* Except for Chinese RoHS

## Specifications

\* All made to order.

### Dimensions



### Equivalent circuits



### Electrical characteristics

Series name	PXV1220S	PBV1632S
Attenuation	1, 2, 3, 4, 5, 6, 7, 8, 9, 10dB	1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 16dB
Attenuation tolerance	±0.5dB (@25°C, no load)	
Impedance	50Ω	
VSWR	1.3max.	
Temperature coefficient of attenuation	N1 ~ N8 (1 ~ 3dB : N1 ~ N9)	N5 0.0041dB/dB*°C N6 0.0035dB/dB*°C N7 0.0026dB/dB*°C N8 0.0019dB/dB*°C
Operating frequency	DC ~ 3GHz	
Rated power	63mW	100mW
Operating temperature	-40°C ~ +100°C	
Packaging	100pcs/bag 1,000pcs/reel	min.20pcs/bag 1,000pcs/reel

· Refer to the data book for details.

## Part numbering system

**PXV 1220S-06dB N1-T**



\* Not for shipment to or sale in the United States\*

High frequency surface mount components

P \* V series