

| | | | | | | | | |
|---------------------------------|-----------|-----------|--|---------------------------|--|---------|-----|------|
| MATED WITH: PASSEND ZU: - | LOC AI | DIST - | REVISIONS ÄNDERUNGEN DESCRIPTION BESCHREIBUNG | | | DATE | DWN | APVD |
| PROJEKT NR.: - | | | P | LTR | | 21MAR11 | RK | HMR |
| | | | K5 | REVISED PER ECO-11-005150 | | | | |

Customer Drawing
for PN 929990


SEE 1355063

RELEASED FOR PUBLICATION
 FREI FÜR VERÖFFENTLICHUNG
 ALL RIGHTS RESERVED.
 ALLE RECHTE VORBEHALTEN

THIS DRAWING IS UNPUBLISHED.
 VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG.

COPYRIGHT - By -

| - | - | - | - | - | - | - |
|------------------|---------|------|------|----------|---------------|-------------|
| CUSTOMER PART NO | PART NO | REV. | PCS. | MATERIAL | SURFACE COLOR | DESCRIPTION |

| | | | | | | | | |
|--|-------------|-----------|--|--------------------------|------------------|----------------|---------------|-----------|
| DIMENSIONS: DIMENSIONEN mm | DWN | 28-APR-04 | MATERIAL | FINISH | OBERFLÄCHE/FARBE | - | | |
| | Abraham,G. | | - | | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN P.P.P. ISO 8015 ISO 2768 - mH -E DIN 16901 - 140 | CHK | 29-APR-04 |  TE Connectivity | | | | | |
| | Goeppel,C. | | | | | | | |
| 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES/WINKEL ± - | APVD | 30-APR-04 | NAME DIA. 1.5 mm SOCKET CONTACT DIA.1.5 mm Buchsenkontakt | | | | | |
| | Bleicher,M. | | | | | | | |
| PRODUCT SPEC PRODUKTSPEZ. - APPLICATION SPEC VERARBEITUNGSSPEZ. - WEIGHT GEWICHT - | SIZE | CAGE CODE | DRAWING NO ZEICHNUNGS-NR. | RESTRICTED TO NUR FÜR | | | | |
| | A4 | 00779 | C-929990 | - | | | | |
| CUSTOMER DRAWING / KUNDENZEICHNUNG | | | | SCALE MASSSTAB | - | SHEET BLATT | 1 OF VON 1 | REV K5 |

