



Product Number: 7022AD (TE internal No. 1423162-7)

Time Delay Relays



<p>Product Type Features: Termination Type = Screw Terminal</p> <p>Electrical Characteristics: Input Voltage (VAC) = 110, 120 Contact Rating = 10A @ 240 VAC</p> <p>Body Features: Series = 7000 Electropneumatic Timing - Industrial</p> <p>Contact Features: Mounting Options = Panel Mount Mode of Operation = Off-Delay Delay Time = 5 seconds to 50 seconds Type of Control = Knob Repeatability, Max. = $\pm 5\%$ Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]</p>	<p>Configuration Features: Contact Arrangement = 2 Form C, DPDT, 2 C/O Multiple Timing Ranges = Without</p> <p>Industry Standards: RoHS/ELV Compliance = Not ELV/RoHS compliant Lead Free Solder Processes = Not relevant for lead free process Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed</p> <p>Conditions for Usage: Temperature Range ($^{\circ}\text{C}$) = -30 - +75</p> <p>Other: Brand = Agastat</p>
--	--