





LOC	DIST	REVISIONS					
HJ	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D1		REVISED PER ECO-11-005150	25MAR11	RK	HMR



Coplanarity ≤ 0.10mm



AXICOM swiss
HF3 XX NNNN
zzV DC YYWW

XX = Relay type
zz = nominal voltage
YYWW = Date code
NNNN = Lot number

DRAWING ALIAS H2000-DOK02

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. BY - COPYRIGHT

DIMENSIONS: mm	DWN UK 9193 16Aug2002	MATERIAL	FINISH		
	CHK HD 9121 16Aug2002				
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m	APVD HD 9121 16Aug2002				
	PRODUCT SPEC				
0 PLC ±-		NAME HF3-Relay 50Ω Dimensions			
1 PLC ±-					
2 PLC ±-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ±-		A4	00779	C-1462051-2	
4 PLC ±-		CUSTOMER DRAWING			SCALE 3:1
ANGLES ±1°					SHEET 1 OF 1
					REV D1