



TAT-125

a) Part as supplied



b) Part after unrestricted recovery.



Colour : Black or Clear.

Outer jacket : Irradiated modified polyolefin type.

Inner liner : Polyamide hot melt adhesive.

Dimensions (in millimetres)

SIZE Nr.	D (min)	d (max)	W nom
	a	b	b
3/16	4,8	2,4	0,93
1/4	6,4	3,2	1,03
3/8	9,5	4,8	1,13
1/2	12,7	6,4	1,21
3/4	19,0	9,5	1,40
1,0	25,4	13,0	1,54
1,1/2	38,0	19,0	1,54

Drawn A.LILLEY

 Checked *[Signature]*

Issue 3

Date December 1988

 Conforms to ISO Recommendations
 3rd Angle Projection
 Not to scale

Approval

Design

[Signature]

MKTG

[Signature]

Q.C.

[Signature]
