


D

C

B

A



RP78601

RP78602

PART NO:	PART NAME:	MATERIAL/SURFACE:	OPTIONAL DESCRIPTION
----------	------------	-------------------	----------------------

PART LIST

TOLERANCES UNLESS OTHERWISE SPECIFIED ACCORDING TO ISO 8015 and ISO 2768-m

DIMENSIONS: mm

test dimen. / Prüfmaß: \square ; auxiliary dimen. / Hilfsmaß: () ; theor. dimen. / theor. Maß: \square ;
 production control dimen. / Fertigungskontr.maß: [] ; dimen. for measure. technology / messtechn. rel. Maß: [] ;

				DEPARTMENT		
				DRAWER	25.09.2007	hel
				CHECKED	25.09.2007	hel
ECO-11-005027	19APR11	HMR		APPROVED	25.09.2007	mader
ECO-NO.:	DATE	NAME	INFO		DATE	NAME



SCALE:	NAME:	DWG NO.:
-	RT Print-Socket	1393234
		OPTIONAL NO.:
		RP78601--/01

REPLACEMENT FOR:	DWG LOC NO.: IF	SHEET: OF	REVISION: A2	A 4
------------------	-----------------	-----------	---------------------	-----