



SBP100143WE5 Product Details

[Share](#) [Print](#) [Email](#)



SBP100143WE5

TE Internal Number: CM9614-000

[Active](#)

Label ID Products

[Always EU RoHS/ELV Compliant](#) (Statement of Compliance)

Product Highlights:

- Printer Type = Thermal Transfer
- Label Height = 36.50 mm
- Label Width = 25.40 mm
- Translucent Vinyl Material
- SBP Series

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Material](#) = Translucent Vinyl
- Series = SBP
- [Color](#) = Clear (White Printable Area)

Electrical Characteristics:

- [Printer Type](#) = Thermal Transfer
- [Number of Labels Across](#) = 3
- [Web Width \(mm \[in\]\)](#) = 87.30 [3.436]

Body Features:

- [Horizontal Repeat \(mm \[in\]\)](#) = 27.9 [1.1]
- Recommended Printer = TE 3000 Series, T200
- Recommended Ribbon = TMS-RJS-RIBBON-4RPSCE

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Printer/Label Features:

- [Label Height \(mm \[in\]\)](#) = 36.50 [1.437]
- [Label Width \(mm \[in\]\)](#) = 25.40 [1.000]
- [Label Finish](#) = Gloss/Matte
- Tamper Evident = No
- [Label Type](#) = Die-Cut
- Adhesive Type = Permanent Acrylic
- [Vertical Repeat \(mm \[in\]\)](#) = 42.20 [1.661]
- [Printable Height \(mm \[in\]\)](#) = 12.70 [0.500]

Environmental:

- [Operating Temperature \(°C \[°F\]\)](#) = -51 - +93 [-60 - +200]

Conditions for Usage:

- Energy Product = No

Packaging Features:

- [Packaging Quantity](#) = 5,000

Other:

- Brand = Raychem

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

