

REV. 2 2/15/99


DCO 15103

COIL: @ +25 °C	
RESISTANCE	700 OHMS ± 10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.5 VDC
MUST RELEASE	1.5 VDC

ENVIRONMENT:	
VIBRATION	10 CPS TO 2000 CPS @ 20 g's
SHOCK	100 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES: _____

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL
TO 5 AMPS 28 VDC RESISTIVE
100,000 OPERATIONS

DR. R.B. 5/28/92 CK. GAH 2-15-99

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD.
CUST. NO. _____

TYPE HFWSA RELAY

HFWSA1201K00