



Product Number: 1658998-1

Shielded Miniature Circular DIN Connectors



Product Type Features:

Product Type = Connector
Number of Positions = 8
Shielded = Yes
PCB Mount Angle = Right Angle
Front Panel Grounding = Without
PCB Retention Feature = Yes
Gender = Receptacle
Stacked = No
Color Code = None
PCB Mount Style = Thru Hole
Shield Material = Copper Alloy

Termination Related Features:

Grounding Clips = Without
Solder Tail Contact Plating = Tin

Body Related Features:

PCB Retention Method = Hold Down Post
Shield Plating = Tin over Nickel

Contact Related Features:

Contact Mating Area Plating Material = Gold (30)
Contact Material = Copper Alloy
Contact Underplating = Nickel (50)

Housing Related Features:

Housing Material = Thermoplastic
Housing Flammability Rating = UL 94V-0
Housing Color = Black

Configuration Related Features:

SPDIF Connector = Without

Industry Standards:

RoHS/ELV Compliance = RoHS compliant, ELV compliant

Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

RoHS/ELV Compliance History = Always was RoHS compliant

Other:

Brand = AMP