



Product Number: 3-1437508-6 (8058-39G3)

Transistor Sockets and Adapters



Product Type Features:

Product Type = Socket
Terminal Type = Contact
Product Series = 8058 Series
Sleeve Material = Brass
Profile = Low

Electrical Characteristics:

Lead Length Accepted (mm [in]) = 3.96 – 5.54 [0.156 – 0.218]
Pin Circle Diameter (mm [in]) = 5.08 [0.200]

Termination Related Features:

Terminal Plating = Gold

Body Related Features:

Terminal Style = Printed Circuit
Number of Terminals = 8
Post Diameter (mm [in]) = 0.51 [0.020]
Socket Type = TO-5
Terminal Material = Beryllium Copper
Insulator Material = Teflon

Contact Related Features:

Sleeve Plating = Gold

Configuration Related Features:

Lead Size Accepted (mm [in]) = 0.41 [0.016]

Industry Standards:

RoHS/ELV Compliance = RoHS compliant, ELV compliant
Lead Free Solder Processes = Wave solder capable to 240°C

Conditions for Usage:

Operating Temperature (°C) = -55 – +125

Other:

Brand = AMP