



- ① MILITARY PART NO., 00779, DATE CODE, PART NO. AND AMP MARKED OPPOSITE SIDE.
- ② HOUSING MAT'L: POLYPHENYLENE SULFIDE, GST-40F PER MIL-M-24519. COLOR: BROWN.
- ③ CONTACT MAT'L: BERYLLIUM COPPER PER ASTM B194 (BeCu) OR COPPER NICKEL SILICONE (CuNiSi)
- ④ CONTACT FINISH: .000050" [0.00127] GOLD IN CONTACT AREA, .000100" [0.0025] TIN-LEAD ON SOLDER TAILS OVER .000030 [0.00076] NICKEL ON ENTIRE CONTACT.
- ⑤ LETTERS INDICATING OUTSIDE ROWS AND NUMBERS INDICATING END CAVITIES MARKED THIS SURFACE.
- ⑥ MEETS ALL REQUIREMENTS OF MIL-C-55302.
- ⑦ LINES INDICATING EVERY FIVE CAVITIES MARKED ON MATING FACE EXCEPT END CAVITIES STARTING AT POSN. #1.

M55302/130-38	6.400 [162.56]	64	6.524 [165.71]	6.625 [168.27]	6.950 [176.53]	7.250 [184.15]	195	1-531134-3
M55302/130-26	4.400 [111.76]	44	4.524 [114.91]	4.625 [117.47]	4.950 [125.73]	5.250 [133.35]	135	1-531134-2
M55302/130-44	7.900 [200.66]	79	8.024 [203.81]	8.125 [206.37]	8.450 [214.63]	8.750 [222.25]	240	531134-8
M55302/130-41	6.900 [175.26]	69	7.024 [178.41]	7.125 [180.97]	7.450 [189.23]	7.750 [196.85]	210	531134-7
M55302/130-35	5.900 [149.86]	59	6.024 [153.01]	6.125 [155.57]	6.450 [163.83]	6.750 [171.45]	180	531134-6
M55302/130-32	5.400 [137.16]	54	5.524 [140.31]	5.625 [142.87]	5.950 [151.13]	6.250 [158.75]	165	531134-5
M55302/130-29	4.900 [124.46]	49	5.024 [127.61]	5.125 [130.17]	5.450 [138.43]	5.750 [146.05]	150	531134-4
M55302/130-23	3.900 [99.06]	39	4.024 [102.21]	4.125 [104.77]	4.450 [113.03]	4.750 [120.65]	120	531134-3
M55302/130-20	3.400 [86.36]	34	3.524 [89.51]	3.625 [92.07]	3.950 [100.33]	4.250 [107.95]	105	531134-2
M55302/130-17	2.900 [73.66]	29	3.024 [76.81]	3.125 [79.37]	3.450 [87.63]	3.750 [95.25]	90	531134-1
MILITARY P/N	F	E	D	C	B	A	POSN.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± .005 [0.13]
4 PLC	± -
ANGLES	± -
FINISH	- ④

MATERIAL: ②-③

APPROVED: T. ALEXANDER 8-5-92

DESIGNED: W. FOLEY 11-10-92

DRAWN: D. MILLER 11-10-92

NAME: Tyco Electronics Corporation, Harrisburg, PA 17105-3608

PRODUCT SPEC: BOX RECEPTACLE ASSY, .100, 3-ROW, .014 X .019 CONTACT TAIL, .025 OFFSET

APPLICATION SPEC: -

SIZE: A1

WEIGHT: -

CUSTOMER DRAWING

SCALE: 4:1

SHEET: 1 OF 1

REV: E