



**Product Number: WP-445102-5-9**

### Label ID Products



#### Product Highlights:

Printer Type = Thermal Transfer  
Label Height = 10.20 mm  
Label Width = 44.50 mm  
Polyester Material  
WP Series

#### Product Type Features:

Material = Polyester  
Color = White  
Comment = Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.

#### Electrical Characteristics:

Printer Type = Thermal Transfer  
Number of Labels Across = 1  
Adhesive Type = Permanent Acrylic  
Web Width (mm [in]) = 50.40 [1.986]

#### Termination Related Features:

Label Type = Die-Cut

#### Body Related Features:

Label Height (mm [in]) = 10.20 [0.402]  
Label Width (mm [in]) = 44.50 [1.750]  
Series = WP  
Recommended Printer = T308S  
Recommended Ribbon = 1330-0607-10

#### Industry Standards:

RoHS/ELV Compliance = RoHS compliant, ELV compliant  
Lead Free Solder Processes = Not relevant for lead free process  
RoHS/ELV Compliance History = Always was RoHS compliant

#### Printer/Label Features:

Vertical Repeat (mm [in]) = 12.70 [0.500]

#### Identification Marking:

Energy Label Type = Pressure Sensitive

**Conditions for Usage:**

Operating Temperature (°C [°F]) = -40 – +150 [-40 – +302]

Energy Product = Yes

**Packaging Related Features:**

Packaging Quantity = 5,000

**Other:**

Tamper Evident = No

Brand = Tyco Electronics