

Part number

Compare 

NL10276AC30-52C

Size (inch)	15.0"
Resolution	1024 x 768 XGA

Technology TN

Viewing Angle (°)	80, 80, 80, 80
Luminance (cd/m²)	1600 
Contrast Ratio	1000:1
Colour Gamut	60%
Surface	AR+Clear

Resp. Time (ms)	8
-----------------	---

Interface	LVDS
Backlight Lifetime (khrs)	50
Backlight Driver	integrated

Operating Temp. (°C)	-30~70 
Stor. Temp.	-30~80

We use cookies to ensure that we give you the best experience on our website. If you continue to use this site we will assume that you agree with it.

Ok

Privacy policy (https://www.tianma.eu/wp-content/uploads/2020/01/Tianma_Europe_Datenschutzerkla%CC%88rung_data_privacy_policy_Website_deutsch-english_082019_v2.pdf)