



**Product Number:** 2001-1302

**3-CONDUCTOR THROUGH TERMINAL BLOCK SUITABLE FOR EX E APPLICATIONS**

**RoHS compliant**

Current intensity EN	24 A
Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm <sup>2</sup> ]	0.25 - 1.5 mm <sup>2</sup>
Cross section [AWG]	22 - 14 AWG
Connection method	CONTACT CAGE CLAMP® CONNECTION
Cross section [mm <sup>2</sup> ]	0.25 - 2.5 mm <sup>2</sup>
Cross section [AWG]	22 - 14 AWG
Wiring method	e+f
Connection method	CONTACT CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	18 A
Weight	4.4 g
Color	orange
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	33 mm
Height	1.299 in
Width	4.2 mm
Width	0.165 in
Depth	59.5 mm
Depth	2.34 in
Strip length from	9 mm
Strip length to	11 mm
Strip length	0.39 in
Mounting	TS 35